



Product Data Sheet

Clip on Pipe Thermometer


63mm dial thermometer with spring for attaching to pipes.

Product Specifications

- Suitable for Pipe Diameter:** 20 - 50 mm
- Temperature Ranges:**
 - 40 to 40°C&F
 - 0 to 120°C&F
 - 0 to 200°C&F
- Accuracy:**
 - 40 to 40°C&F: +/-2°C
 - otherwise +/-4°C
- Product Material:** Plastic Case with Plastic Window or Metal Case with Glass Window
- Bezel Material:** Chrome
- Sensor Mechanism:** Standard bimetal coil
- Filling:** Dry
- Hazard Information (SDS):** See www.brannan.co.uk for information
- Dial Dimensions - with Bezel:** 66mm diameter x 30mm
- Dial Dimensions - no Bezel:** 62mm diameter x 29mm
- Box Dimensions:** 82mm x 80mm x 30mm



Image shows 33/401/0



| Description | Product Weight* | Range | Accuracy | Product No |
|--|-----------------|---------------|----------|------------|
| Plastic Cased Clip on Pipe Thermometer | 62g | 0 to 120°C&F | +/-4°C | 33/401/0 |
| | | 0 to 200°C&F | +/-4°C | 33/402/0 |
| Plastic Case - without Bezel | 56g | 0 to 120°C&F | +/-4°C | 33/404/0 |
| Metal Cased Clip on Pipe Thermometer | 94g | -40 to 40°C&F | +/-2°C | 33/403/0 |
| | | 0 to 120°C&F | +/-4°C | 33/501/0 |

* Product Weight includes 5g Spring & 11g Box

PDS 0178:15:R3

Brannan Thermometers & Instrumentation

Leconfield Industrial Estate • Cleator Moor • Cumbria • CA25 5QE • UK

tel: +44 (0)1946 816600 fax: +44 (0)1946 816625 email: sales@brannan.co.uk web: www.brannan.co.uk

