

Current Transducer HAS 50 ... 600-S

For the electronic measurement of currents: DC, AC, pulsed..., with galvanic separation between the primary circuit and the secondary circuit.



Ele	ectrical data						
	Type	Primary nom	inal Prim	ary current,			
		RMS curre	nt meas	uring range	1)		
		$I_{PN}(A)$		$I_{PM}(A)$			
	HAS 50-S	50		±150			
	HAS 100-S	100		±300			
	HAS 200-S	200		±600			
	HAS 300-S	300		±900			
	HAS 400-S	400		±900			
	HAS 500-S	500		±900			
	HAS 600-S	600		±900			
$U_{\rm c}$	Supply voltage (±5 %) 1)		±15)	V	
$I_{\rm C}$	Current consumption			±15)	mA	
R_{INS}	Insulation resistance	@ 500 V DC		> 1	000	$M\Omega$	
U_{out}	Output voltage (Analo	og) @ $\pm I_{PN}$, R_{L} :	= $10 \text{ k}\Omega$, T_A =	25 °C ±4		V	
$R_{\rm out}$	Output internal resista	ance	approx	100)	Ω	
R_{L}	Load resistance 2)			> 1		kΩ	
Accuracy - Dynamic performance data							
$\varepsilon_{ m tot}$	Total error @ I_{PN} , T_{A} =	= 25 °C (exclu	iding offset)	< <u>+</u>	1 %	of I_{PN}	
$\varepsilon_{\scriptscriptstyle \! L}$	Linearity error 3) (0			< <u>+</u>	1 %	of I_{PN}	
U_{OE}	Electrical offset voltage	ge, $T_{A} = 25 ^{\circ}\text{C}$	HAS 50-S	< ±		mV	
				$.600-S < \pm 2$	20	mV	
U_{OM}	Hysteresis offset voltage @ $I_P = 0$,						
			xcursion of '	1 14		mV	
TCU_{OE}	Temperature coefficie	ent of $U_{\sf OE}$	HAS 50-S	< ±		mV/K	
				. 600-S < ±	1	mV/K	
TCU_{out}	Temperature coefficie			< <u>+</u>		%/K	
$t_{\rm D~90}$	Delay time to 90 % of the final output value for $I_{\rm PN}$ step $^{4)}$ < 3 $$ μs						
BW	Frequency bandwidth	ı (-3 dB) ⁵⁾		DC	50	kHz	
Ge	neral data						
T_{A}	Ambient operating ter	mperature) +80	°C	
T_{Ast}	Ambient storage temp	perature		-25	+80	°C	
m	Mass		approx	60		g	
	Standards	UL			508:2010		
	EMC Safety			IEC	IEC 61000-6-2:2016		
				IEC	IEC 61800-3:2017 6)		
				IEC	IEC 61010-1:2010		
	Environmental				IEC 61477-1:2012		
		Environm	ental	IEC	61477-1:2	2012	

Notes: 1) Operating at $\pm 12 \text{ V} \le U_{\text{C}} < \pm 15 \text{ V}$ will reduce the measuring range

- $^{2)}$ If the customer uses 1 k Ω of the load resistor, the primary current has to be limited as the nominal. To measure the full defined measuring range, the load resistor should be at minimum 10 k Ω
- 3) Linearity data exclude the electrical offset
- 4) For a $di/dt = 50 \text{ A/}\mu\text{s}$
- 5) Under small signals condition
- ⁶⁾ Regarding compliance towards IEC 61000-4-3 (IEC 61800-3:2017): variation of the offset between 390 MHz and 400 MHz with a field intensity of 10 [V/m].
 N° 74.74.25.000.0, N° 74.74.34.000.0, N° 74.74.44.000.0, N° 74.74.46.000.0, N° 74.74.48.000.0, N° 74.74.50.000.0, N° 74.74.50.000.0

 $I_{PN} = 50 \dots 600 A$



Features

- Hall effect measuring principle
- Insulating plastic case made of polycarbonate PBT recognized according to UL 94-V0.

Advantages

- Easy mounting
- Low power consumption
- Small size and space saving
- Only one design for wide current ratings range
- High immunity to external interference.

Applications

- AC variable speed drives
- Static converters for DC motor drives
- Battery supplied applications
- Uninterruptible Power Supplies (UPS)
- Switched Mode Power Supplies (SMPS)
- Power supplies for welding applications.

Application domain

Industrial.



Current Transducer HAS 50 ... 600-S

Insulation coordination						
U_{d}	RMS voltage for AC insulation test, 50 Hz, 1 min	3.6	kV			
$U_{\rm Ni}$	Impulse withstand voltage 1.2/50 μs	> 6.6	kV			
		Min				
d_{CD}	Creepage distance	7.08	mm			
$d_{ extsf{Cp}} \ d_{ extsf{Cl}}$	Clearance	6.23	mm			
CTI	Comparative tracking index (group IIIa)	275				

Applications examples

According to IEC 61010-1 standard and following conditions:

- Over voltage category OV 3
- Pollution degree PD2
- Non-uniform field

	IEC 61010-1		
$\overline{d_{\rm Cp},d_{\rm Cl},U_{\rm Ni}}$	Nominal voltage		
Basic insulation	600 V		
Reinforced insulation	300 V		

Safety

This transducer must be used in limited-energy secondary circuits according to IEC 61010-1.



This transducer must be used in electric/electronic equipment with respect to applicable standards and safety requirements in accordance with the manufacturer's operating instructions.



Caution, risk of electrical shock

When operating the transducer, certain parts of the module can carry hazardous voltage (eg. primary busbar, power supply).

Ignoring this warning can lead to injury and/or cause serious damage.


This transducer is a build-in device, whose conducting parts must be inaccessible after installation.

A protective housing or additional shield could be used.

Main supply must be able to be disconnected.



Dimensions HAS 50 ... 600-S (in mm)



Mechanical characteristics

General tolerance

±0.5 mm

Transducer fastening

1 hole Ø 4.5 mm

· Connection of secondary

1 M4 steel screw Recommended fastening torque 0.75 N·m (±10 %)

Molex type 2501P04V00A 1)

1) Recommended mating connector: Molex 511910400 (housing) Note: and 508029101 (contact).

Remarks

- $\bullet \ \ U_{\rm out}$ is positive when $I_{\rm P}$ flows in the direction of the arrow.
- Temperature of the primary conductor should not exceed 100 °C.
- Installation of the transducer must be done unless otherwise specified on the datasheet, according to LEM Transducer Generic Mounting Rules. Please refer to LEM document N°ANE120504 available on our Web site: https://www.lem.com/en/file/3137/download/.
- Dynamic performances (di/dt and delay time) are best with a single bar completely filling the primary hole.
- This is a standard model. For different versions (supply voltages, turns ratios, unidirectional measurements...), please contact us.