

## Concentricity gauge

### Application:

For measuring the axial and radial run-out precision of shafts.

### Version:

- 2 movable tailstocks and 1 measuring stand for holding a dial gauge or precision pointer
- 1 tailstock with fixed tip and 1 tailstock with movable tip, adjustable using hand lever (sleeve and centre point made from one piece)
- Evenness tolerance of measuring surfaces in line with DIN 876-2. Tailstocks with 75 mm tip height have vee block surfaces
- Location hole for a dial gauge or precision pointer 8 H 7

|                          |                  |
|--------------------------|------------------|
| <b>Art. no.</b>          | <b>35480 020</b> |
| <b>Point height</b>      | 100 mm           |
| <b>Max. point width</b>  | 450 mm           |
| <b>Base plate length</b> | 700 mm           |
| <b>Base plate width</b>  | 180 mm           |
| <b>Groove width</b>      | 12 mm            |
| <b>Weight</b>            | 35 kg            |



### EAN-Code

4029713265045