



MOTOR STARTER SIRIUS 3RM1 REVERSING
STARTER SAFETY 500 V; 0,1 - 0,5 A; 24 V DC PUSH-
IN-TYPE CONNECTION SYSTEM

Figure similar

| General technical data: | | |
|---|----|---|
| product brand name | | SIRIUS |
| Product designation | | Motor starter |
| Design of the product | | with reversing functionality and electronic overload protection and safety-related shutdown |
| Trip class | | CLASS 10A |
| Protection class IP | | IP20 |
| Suitability for operation Device connector 3ZY12 | | Yes |
| Product function Intrinsic device protection | | Yes |
| Type of the motor protection | | solid-state |
| Product function Adjustable current limitation | | Yes |
| Installation altitude at height above sea level maximum | m | 2 000 |
| Ambient temperature | | |
| • during operation | °C | -25 ... +60 |
| • during transport | °C | -40 ... +70 |
| • during storage | °C | -40 ... +70 |
| Shock resistance | | 6g / 11 ms |
| Vibration resistance | | 1 ... 6 Hz, 15 mm; 20 m/s ² , 500 Hz |
| Surge voltage resistance Rated value | kV | 6 |
| Insulation voltage Rated value | V | 500 |
| Mechanical service life (switching cycles) typical | | 30 000 000 |
| Conducted interference due to conductor-conductor surge acc. to IEC 61000-4-5 | | 2 kV |
| Conducted interference due to burst acc. to IEC 61000-4-4 | | 3 kV / 5 kHz |

| | | |
|---|---|--|
| Conducted interference due to high-frequency radiation acc. to IEC 61000-4-6 | | 10 V |
| Electrostatic discharge acc. to IEC 61000-4-2 | | 6 kV contact discharge / 8 kV air discharge |
| Field-bound HF-interference emission acc. to CISPR11 | | Class B for the domestic, business and commercial environments |
| Conducted HF-interference emissions acc. to CISPR11 | | Class B for the domestic, business and commercial environments |
| maximum permissible voltage for safe isolation | | |
| • between main and auxiliary circuit | V | 500 |
| • between control and auxiliary circuit | V | 250 |
| Equipment marking acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750 | | Q |
| Equipment marking acc. to DIN EN 61346-2 | | Q |

Safety related data:

| | | |
|---|-----|-------------|
| Safety Integrity Level (SIL) acc. to IEC 61508 | | SIL3 |
| Performance level (PL) acc. to EN ISO 13849-1 | | e |
| Category acc. to EN ISO 13849-1 | | 4 |
| T1 value for proof test interval or service life acc. to IEC 61508 | y | 20 |
| PFHD with high demand rate acc. to EN 62061 | 1/h | 0.00000002 |
| Protection against electrical shock | | finger-safe |
| Safety device type acc. to IEC 61508-2 | | Type B |
| OFF-delay time with safety-related request when switched off via control inputs maximum | ms | 65 |
| OFF-delay time with safety-related request when switched off via supply voltage maximum | ms | 120 |

Main circuit:

| | | |
|---|-----|-------------|
| Number of poles for main current circuit | | 3 |
| Operating voltage Rated value maximum | V | 500 |
| Operating frequency | | |
| • 1 Rated value | Hz | 50 |
| • 2 Rated value | Hz | 60 |
| Operating current with AC at 400 V Rated value | A | 0.5 |
| Minimum load in % of I _M | % | 20 |
| Active power loss typical | W | 0.02 |
| Adjustable response value current of the current-dependent overload release | A | 0.1 ... 0.5 |
| Operating power for three-phase motors at 400 V at 50 Hz | kW | 0 ... 0.12 |
| Operating frequency maximum | 1/s | 1 |

Control circuit/ Control:

| | | |
|---|--|----|
| Type of voltage of the control supply voltage | | DC |
| Control supply voltage 1 | | |

| | | |
|---|----|--------------|
| <ul style="list-style-type: none"> • for DC Rated value | V | 24 |
| Operating range factor control supply voltage rated value | | |
| <ul style="list-style-type: none"> • for DC | | 0.8 ... 1.25 |
| Control current | | |
| <ul style="list-style-type: none"> • for DC <ul style="list-style-type: none"> — in standby mode — during operation — when switching on | mA | 13 |
| | mA | 57 |
| | mA | 150 |
| Input voltage at digital input | | |
| <ul style="list-style-type: none"> • for signal <1> <ul style="list-style-type: none"> — for DC • with signal <0> <ul style="list-style-type: none"> — for DC | V | 15 ... 30 |
| | V | 0 ... 5 |
| Input current at digital input | | |
| <ul style="list-style-type: none"> • for signal <1> <ul style="list-style-type: none"> — for DC • with signal <0> <ul style="list-style-type: none"> — for DC | mA | 8 |
| | mA | 1 |
| Switch-on delay time | ms | 90 ... 120 |
| OFF-delay time | ms | 40 ... 55 |

| Auxiliary circuit: | | |
|--|---|------------|
| Number of CO contacts for auxiliary contacts | | 1 |
| Design of the switching contact as NO contact for signaling function | | Electronic |
| Operating current of the auxiliary contacts | | |
| <ul style="list-style-type: none"> • at AC-15 maximum • at DC-13 maximum | A | 3 |
| | A | 1 |






| Installation/ mounting/ dimensions: | | |
|-------------------------------------|----|--|
| mounting position | | vertical, horizontal, standing |
| Mounting type | | screw and snap-on mounting onto 35 mm standard mounting rail |
| Width | mm | 22.5 |
| Height | mm | 100 |
| Depth | mm | 141.6 |

| Connections/ Terminals: | | |
|---|--|---|
| Type of electrical connection | | |
| <ul style="list-style-type: none"> • for main current circuit • for auxiliary and control current circuit | | PUSH-IN connection (spring-loaded connection) |
| | | PUSH-IN connection (spring-loaded connection) |
| Type of connectable conductor cross-section for main contacts | | |
| <ul style="list-style-type: none"> • solid | | 1x (0.5 ... 4 mm ²) |

| | | |
|---|----------|--|
| <ul style="list-style-type: none"> • finely stranded <ul style="list-style-type: none"> — with core end processing — without core end processing | | 1x (0.5 ... 2.5 mm ²) 1x (0.5 ... 4 mm ²) |
| Type of connectable conductor cross-section for AWG conductors for main contacts | | 1x (20 ... 12) |
| Type of connectable conductor cross-section for auxiliary contacts | | |
| <ul style="list-style-type: none"> • solid • finely stranded <ul style="list-style-type: none"> — with core end processing — without core end processing | | 1x (0.5 ... 1.5 mm ²), 2x (0.5 ... 1.5 mm ²) 1x (0,5 ... 1,0 mm ²), 2x (0,5 ... 1,0 mm ²) 1x (0.5 ... 1.5 mm ²), 2x (0.5 ... 1.5 mm ²) |
| Type of connectable conductor cross-section for AWG conductors for auxiliary contacts | | 1x (20 ... 16), 2x (20 ... 16) |

| | | |
|--|---|-----|
| UL ratings: | | |
| Full-load current (FLA) for three-phase AC motor at 480 V Rated value | A | 0.5 |



Certificates/ approvals:

| | | | |
|--|---|---|---|
| General Product Approval | For use in hazardous locations | Functional Safety/Safety of Machinery | Declaration of Conformity |
|  CCC |  UL |  |  ATEX |
| | | Type Examination |  EG-Konf. |

| | |
|--|---|
| Test Certificates | other |
| Type Test Certificates/Test Report | Special Test Certificate |
| | Confirmation |
| | Environmental Confirmations |

Further information

- Information- and Downloadcenter (Catalogs, Brochures,...)**
<http://www.siemens.com/industrial-controls/catalogs>
- Industry Mall (Online ordering system)**
<http://www.siemens.com/industrymall>
- Cax online generator**
<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RM13012AA04>
- Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**
<http://support.automation.siemens.com/WW/view/en/3RM13012AA04/all>
- Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**
<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RM13012AA04&lang=en>



last modified:

15.01.2015