

according to Regulation (EC) No. 453/2010

Date of issue: 18/03/2015 Revision date: Version: 1.0

SECTION 1: Identification of the substance/mixture and of the company/undertaking

Product identifier

Product form : Mixture : P40 Product name : Bodyfiller Product group

Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Industrial/Professional use spec : Industrial

For professional use only

Function or use category : Fillers

1.2.2. Uses advised against

No additional information available

Details of the supplier of the safety data sheet

U-POL LIMITED Denington Road **Northants**

NN8 2QH Wellingborough - UK

T +44 (0) 1933 230310 - F +44 (0) 1933 425797 technical.department@u-pol.com - www.u-pol.com

1.4. **Emergency telephone number**

Emergency number : +44 1933 230310 (07:30 - 17:00hrs UK time)

SECTION 2: Hazards identification

Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Skin Irrit. 2 H315 Eye Irrit. 2 H319 Repr. 2 H361 STOT RE 1 H372

Full text of H-phrases: see section 16

Classification according to Directive 67/548/EEC [DSD] or 1999/45/EC [DPD]

Repr.Cat.3; R63

F: R11

Full text of R-phrases: see section 16

Adverse physicochemical, human health and environmental effects

No additional information available

Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP)





GHS08

GHS07

: Danger

Signal word (CLP) Hazardous ingredients : styrene

Hazard statements (CLP) H315 - Causes skin irritation H319 - Causes serious eye irritation

H361 - Suspected of damaging fertility or the unborn child

H372 - Causes damage to organs through prolonged or repeated exposure

P202 - Do not handle until all safety precautions have been read and understood Precautionary statements (CLP)

P263 - Avoid contact during pregnancy/while nursing P264 - Wash hands thoroughly after handling

P280 - Wear eye protection, protective clothing, protective gloves

23/04/2015 EN (English) SDS Ref.: P40 1/8

according to Regulation (EC) No. 453/2010

P302+P352 - IF ON SKIN: Wash with plenty of water

P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove

contact lenses, if present and easy to do. Continue rinsing

P501 - Dispose of contents/container to hazardous or special waste collection point, in

accordance with local, regional, national and/or international regulation

: EUH208 - Contains BISPHENOL A - (EPICHLOROHYDRIN); EPOXY RESIN. May produce an

allergic reaction

No labelling applicable

EUH phrases

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substance

Not applicable

3.2. Mixture

Name	Product identifier	%	Classification according to Directive 67/548/EEC	
styrene	(CAS No) 100-42-5 (EC no) 202-851-5	5 - 43	Repr.Cat.3; R63 Xn; R20 Xn; R48/20 Xi; R36/38 R10	
xylene substance with a Community workplace exposure limit	(CAS No) 1330-20-7 (EC no) 215-535-7 (EC index no) 601-022-00-9	< 5	R10 Xn; R20/21 Xi; R38	
BISPHENOL A - (EPICHLOROHYDRIN); EPOXY RESIN	(CAS No) 025068-38-6	< 5	Xi; R36/38 R43 N; R51/53	
ethylbenzene substance with a Community workplace exposure limit	(CAS No) 100-41-4 (EC no) 202-849-4 (EC index no) 601-023-00-4	< 5	F; R11 Xn; R20	
Name	Product identifier	Specific co	Specific concentration limits	
xylene	(CAS No) 1330-20-7 (EC no) 215-535-7 (EC index no) 601-022-00-9	(C >= 12.5) X	(C >= 12.5) Xn;R20/21	
Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]	
styrene	(CAS No) 100-42-5 (EC no) 202-851-5	5 - 43	Flam. Liq. 3, H226 Acute Tox. 4 (Inhalation), H332 Skin Irrit. 2, H315 Eye Irrit. 2, H319 Repr. 2, H361d STOT RE 1, H372	
xylene substance with a Community workplace exposure limit	(CAS No) 1330-20-7 (EC no) 215-535-7 (EC index no) 601-022-00-9	< 5	Flam. Liq. 3, H226 Acute Tox. 4 (Dermal), H312 Acute Tox. 4 (Inhalation:dust,mist), H332 Skin Irrit. 2, H315	
BISPHENOL A - (EPICHLOROHYDRIN); EPOXY RESIN	(CAS No) 025068-38-6	< 5	Skin Irrit. 2, H315 Eye Irrit. 2, H319 Skin Sens. 1, H317 Aquatic Chronic 2, H411	
ethylbenzene substance with a Community workplace exposure limit	(CAS No) 100-41-4 (EC no) 202-849-4 (EC index no) 601-023-00-4	< 5	Flam. Liq. 2, H225 Acute Tox. 4 (Inhalation), H332 STOT RE 2, H373 Asp. Tox. 1, H304	

Full text of R- and H-phrases: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general

: Never give anything by mouth to an unconscious person. IF exposed or concerned: Get medical advice/attention.

First-aid measures after inhalation

: Allow victim to breathe fresh air. Allow the victim to rest.

First-aid measures after skin contact

: Wash with plenty of soap and water. Wash contaminated clothing before reuse. If skin irritation occurs: Get medical advice/attention. Get medical advice/attention.

23/04/2015 EN (English) SDS Ref.: P40 2/8

Safety Data Sheet

according to Regulation (EC) No. 453/2010

First-aid measures after eye contact : Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to

do. Continue rinsing. If eye irritation persists: Get medical advice/attention. Get medical

advice/attention.

First-aid measures after ingestion : Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/injuries : Suspected of damaging fertility or the unborn child. Causes damage to organs through

prolonged or repeated exposure.

Symptoms/injuries after skin contact : Causes skin irritation.

Symptoms/injuries after eye contact : Causes serious eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

No additional information available

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Foam. Dry powder. Carbon dioxide. Water spray. Sand.

Unsuitable extinguishing media : Do not use a heavy water stream.

5.2. Special hazards arising from the substance or mixture

No additional information available

5.3. Advice for firefighters

Firefighting instructions : Use water spray or fog for cooling exposed containers. Exercise caution when fighting any

chemical fire. Prevent fire-fighting water from entering environment.

Protection during firefighting : Do not enter fire area without proper protective equipment, including respiratory protection.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General measures : Remove ignition sources.

6.1.1. For non-emergency personnel

Protective equipment : Safety glasses. Protective clothing. Gloves.

Emergency procedures : Evacuate unnecessary personnel.

6.1.2. For emergency responders

Protective equipment : Equip cleanup crew with proper protection.

Emergency procedures : Ventilate area.

6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : On land, sweep or shovel into suitable containers. Minimize generation of dust. Store away

from other materials.

6.4. Reference to other sections

See Heading 8. Exposure controls and personal protection. For further information refer to section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Wash hands and other exposed areas with mild soap and water before eating, drinking or

smoking and when leaving work. Provide good ventilation in process area to prevent formation of vapour. Obtain special instructions before use. Do not handle until all safety precautions

have been read and understood. Do not breathe dust, fume.

Hygiene measures : Wash hands thoroughly after handling. Do not eat, drink or smoke when using this product.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Keep only in the original container in a cool, well ventilated place away from : Ignition sources,

Heat sources. Keep container closed when not in use.

Incompatible products : Strong bases. Strong acids.
Incompatible materials : Sources of ignition. Direct sunlight.

Storage temperature : < 25 °C

Special rules on packaging : Keep only in original container.

7.3. Specific end use(s)

No additional information available

23/04/2015 EN (English) SDS Ref.: P40 3/8

according to Regulation (EC) No. 453/2010

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

styrene (100-42-5)					
United Kingdom	Local name	Styrene			
United Kingdom	WEL TWA (mg/m³)	430 mg/m³			
United Kingdom	WEL TWA (ppm)	100 ppm			
United Kingdom	WEL STEL (mg/m³)	1080 mg/m³			
United Kingdom	WEL STEL (ppm)	250 ppm			
ethylbenzene (100-41-4)	ethylbenzene (100-41-4)				
EU	Local name	Ethylbenzene			
EU	IOELV TWA (mg/m³)	442 mg/m³			
EU	IOELV TWA (ppm)	100 ppm			
EU	IOELV STEL (mg/m³)	884 mg/m³			
EU	IOELV STEL (ppm)	200 ppm			
EU	Notes	Skin			
United Kingdom	Local name	Ethylbenzene			
United Kingdom	WEL TWA (mg/m³)	441 mg/m³			
United Kingdom	WEL TWA (ppm)	100 ppm			
United Kingdom	WEL STEL (mg/m³)	552 mg/m³			
United Kingdom	WEL STEL (ppm)	125 ppm			
United Kingdom	Remark (WEL)	Sk			
xylene (1330-20-7)					
EU	Local name	Xylene, mixed isomers, pure			
EU	IOELV TWA (mg/m³)	221 mg/m³			
EU	IOELV TWA (ppm)	50 ppm			
EU	IOELV STEL (mg/m³)	442 mg/m³			
EU	IOELV STEL (ppm)	100 ppm			
EU	Notes	Skin			
United Kingdom	Local name	Xylene, o-,m-,p- or mixed isomers			
United Kingdom	WEL TWA (mg/m³)	220 mg/m³			
United Kingdom	WEL TWA (ppm)	50 ppm			
United Kingdom	WEL STEL (mg/m³)	441 mg/m³			
United Kingdom	WEL STEL (ppm)	100 ppm			
United Kingdom	Remark (WEL)	Sk, BMGV			

8.2. Exposure controls

Personal protective equipment : Avoid all unnecessary exposure.

Materials for protective clothing : Impermeable clothing
Hand protection : Wear protective gloves

Eye protection : Chemical goggles or safety glasses
Skin and body protection : Wear suitable protective clothing

Respiratory protection : Wear appropriate mask

Other information : Do not eat, drink or smoke during use.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state : Solid

Appearance : Fibrous. Paste.
Colour : Clear to light yellow.

Odour : aromatic.

Odour threshold : No data available pH : No data available Relative evaporation rate (butylacetate=1) : No data available Melting point : No data available Freezing point : No data available Boiling point : No data available : No data available

Flash point : 32 °C

23/04/2015 EN (English) SDS Ref.: P40 4/8

Safety Data Sheet

according to Regulation (EC) No. 453/2010

Auto-ignition temperature : No data available
Decomposition temperature : No data available
Flammability (solid, gas) : Non flammable
Vapour pressure : No data available
Relative vapour density at 20 °C : No data available
Relative density : No data available
Density : 1.23 - 1.27

Solubility : insoluble in water. soluble in most organic solvents.

Log Pow : No data available
Viscosity, kinematic : No data available
Viscosity, dynamic : No data available
Explosive properties : No data available
Oxidising properties : No data available
Explosive limits : No data available

9.2. Other information

VOC content : 388 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

No additional information available

10.2. Chemical stability

Not established.

10.3. Possibility of hazardous reactions

Not established.

10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures.

10.5. Incompatible materials

Strong acids. Strong bases.

10.6. Hazardous decomposition products

fume. Carbon monoxide. Carbon dioxide.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity : Not classified

Skin corrosion/irritation : Causes skin irritation.
Serious eye damage/irritation : Causes serious eye irritation.

Respiratory or skin sensitisation : Not classified

Based on available data, the classification criteria are not met

Germ cell mutagenicity : Not classified

Based on available data, the classification criteria are not met

Carcinogenicity : Not classified

Based on available data, the classification criteria are not met

Reproductive toxicity : Suspected of damaging fertility or the unborn child.

Specific target organ toxicity (single exposure) : Not classified

Based on available data, the classification criteria are not met

Specific target organ toxicity (repeated

exposure)

: Causes damage to organs through prolonged or repeated exposure.

Aspiration hazard : Not classified

Based on available data, the classification criteria are not met

Potential adverse human health effects and

symptoms

: Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

12.1. Toxicity

No additional information available

23/04/2015 EN (English) SDS Ref.: P40 5/8

Safety Data Sheet

according to Regulation (EC) No. 453/2010

12.2. Persistence and degra

P40

Persistence and degradability Not established.

12.3. Bioaccumulative potential

P40

Bioaccumulative potential Not established.

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

Additional information : Avoid release to the environment

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Regional legislation (waste) : Disposal must be done according to official regulations.

Waste disposal recommendations : Dispose in a safe manner in accordance with local/national regulations. Dispose of

contents/container to Remove waste in accordance with local and/or national regulations.

Ecology - waste materials : Avoid release to the environment.

SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

14.1. UN number

Not regulated for transport

14.2. UN proper shipping name

Proper Shipping Name (ADR) : Not applicable
Proper Shipping Name (IMDG) : Not applicable
Proper Shipping Name (IATA) : Not applicable
Proper Shipping Name (ADN) : Not applicable
Proper Shipping Name (RID) : Not applicable

14.3. Transport hazard class(es)

ADR

Transport hazard class(es) (ADR) : Not applicable

IMDG

Transport hazard class(es) (IMDG) : Not applicable

IATA

Transport hazard class(es) (IATA) : Not applicable

ADN

Transport hazard class(es) (ADN) : Not applicable

RID

Transport hazard class(es) (RID) : Not applicable

14.4. Packing group

Packing group (ADR) : Not applicable
Packing group (IMDG) : Not applicable
Packing group (IATA) : Not applicable
Packing group (ADN) : Not applicable
Packing group (RID) : Not applicable

14.5. Environmental hazards

Dangerous for the environment : No Marine pollutant : No

Other information : No supplementary information available

23/04/2015 EN (English) SDS Ref.: P40 6/8

according to Regulation (EC) No. 453/2010

14.6. Special precautions for user

14.6.1. Overland transport

14.6.2. Transport by sea

14.6.3. Air transport

14.6.4. Inland waterway transport

Carriage prohibited (ADN) : No Not subject to ADN : No

14.6.5. Rail transport

Carriage prohibited (RID) : No

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no substances with Annex XVII restrictions Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

VOC content : 388 g/l

Seveso Information : This product is not subject to the Seveso Directive

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Data sources : REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE

COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending

Regulation (EC) No 1907/2006.

Other information : None.

Full text of R-, H- and EUH-phrases:

Acute Tox. 4 (Dermal)	Acute toxicity (dermal), Category 4
Acute Tox. 4 (Inhalation)	Acute toxicity (inhal.), Category 4
Acute Tox. 4 (Inhalation:dust,mist)	Acute toxicity (inhalation:dust,mist) Category 4
Aquatic Chronic 2	Hazardous to the aquatic environment — Chronic Hazard, Category 2
Asp. Tox. 1	Aspiration hazard, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Flam. Liq. 2	Flammable liquids, Category 2
Flam. Liq. 3	Flammable liquids, Category 3
Repr. 2	Reproductive toxicity, Category 2
Repr. 2	Reproductive toxicity, Category 2
Skin Irrit. 2	Skin corrosion/irritation, Category 2
Skin Sens. 1	Sensitisation — Skin, category 1
STOT RE 1	Specific target organ toxicity — Repeated exposure, Category 1
STOT RE 2	Specific target organ toxicity — Repeated exposure, Category 2
H225	Highly flammable liquid and vapour
H226	Flammable liquid and vapour
H304	May be fatal if swallowed and enters airways
H312	Harmful in contact with skin
H315	Causes skin irritation

23/04/2015 EN (English) SDS Ref.: P40 7/8

Safety Data Sheet

according to Regulation (EC) No. 453/2010

H317	May cause an allergic skin reaction
H319	Causes serious eye irritation
H332	Harmful if inhaled
H361	Suspected of damaging fertility or the unborn child
H361d	Suspected of damaging the unborn child
H372	Causes damage to organs through prolonged or repeated exposure
H373	May cause damage to organs through prolonged or repeated exposure
H411	Toxic to aquatic life with long lasting effects
EUH208	Contains . May produce an allergic reaction
R10	Flammable
R11	Highly flammable
R20	Harmful by inhalation
R20/21	Harmful by inhalation and in contact with skin
R36/38	Irritating to eyes and skin
R38	Irritating to skin
R43	May cause sensitisation by skin contact
R48/20	Harmful: danger of serious damage to health by prolonged exposure through inhalation
R51/53	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment
R63	Possible risk of harm to the unborn child
F	Highly flammable
N	Dangerous for the environment
Xi	Irritant
Xn	Harmful

UPOL SDS EU (no product code)

For professional use only.

The information contained within this Safety Data Sheet (SDS) is believed to be correct as of the date issued however it is subject to change from time to time. It does not purport to be all inclusive or exhaustive and shall only be used as a guide. U-POL makes no warranties, expressed or implied, including but not limited to, any implied warranty of fitness for a given purpose or usage. It is the Buyers responsibility to ensure the suitability of the products for their own use and to check the information is up to date. U-POL cannot be held responsible for the suitability of use for any of its products, considering the wide range of factors such as application, substrates and handling methods. Since these conditions of use are outside of our control, the company shall not be held liable for any damage resulting from handling or from contact with the product detailed. Moreover, addition of reducers, hardeners or other additives over and above U-POL's recommendations for use, may substantially alter the composition and hazards of the product. U-POL data sheets are available via the U-POL website at WWW.U-POL.COM.

23/04/2015 EN (English) SDS Ref.: P40 8/8