



Figure similar

TRANSFORMER SITAS; PHASES:1;  
 PN/PN(S6)(KVA):0,063 /0,19; UPRI(V):230+/-5%;  
 USEC(V):230; ISEC(A):0,274; F(HZ):50...60; VECTOR  
 GR./SHIELD WNG.:II0 /0; TA/ISOKL:40 /B; IP00; TYPE  
 OF TERMINALS:CAGE-CLAMP;  
 INSTALLATION:SCREWS/MOUNTING RAILS; EN  
 61558-2-1, -2-2, -2-4 >UL/CSA-RECOGNIZED<  
 >CONTROL CIRCUIT TRANSFORMER< >ISOLATION  
 TRANSFORMER<

### General technical data:

Product designation		transformer SITAS
product brand name		SIDAC
Operating apparent output Rated value	V·A	63
Efficiency		0.85
Connection method for transformers		II0
Certificate of suitability		CE / cRUus
Product function		
• Temperature monitoring		No
• Insulation monitoring		No
• Short-circuit and overload proof		No
Number of shielding windings		0
Short-term vector power	V·A	190

### Inputs:

Phase number of the inputs		1
Input voltage		
• _1 Rated value	V	242
• _2 Rated value	V	230
• _3 Rated value	V	218
Electrical input frequency		
• minimum	Hz	50
• maximum	Hz	60

### Outputs:

Phase number of the outputs		1
-----------------------------	--	---

<b>Output voltage</b>		
• _1 Rated value	V	230
<b>Electrical output frequency</b>		
• maximum	Hz	60
• minimum	Hz	50

#### Ambient conditions:

<b>Thermal class acc. to IEC 60085</b>		B
<b>Ambient temperature Rated value</b>	°C	40
<b>Protection class IP</b>		IP00

#### Mechanical data:

<b>Type of electrical connection</b>		
• at output for main current circuit		Cage-Clamp terminals
• at input for main current circuit		Cage Clamp terminals
<b>Mounting type</b>		screws / standard rail
<b>Construction form of the iron core</b>		EI 84/28
<b>Width</b>	m	0.086
<b>Height</b>	m	0.098
<b>Depth</b>	m	0.09

#### Certificates/ approvals:

<b>General Product Approval</b>	<b>Shipping Approval</b>	<b>other</b>
---------------------------------	--------------------------	--------------



[other](#)

#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4AM32424TT100FA1>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/4AM32424TT100FA1>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=4AM32424TT100FA1&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AM32424TT100FA1&lang=en)

**last modified:**

15.01.2015