CONDUCTIVE POLYMER ALUMINUM SOLID ELECTROLYTIC CAPACITORS

nichicon

NEV



- •Low ESR, High Capacitance, High ripple current.
- •Large Sized.
- •Load life of 2000 hours at 105°C.
- •Radial lead type : Lead free flow soldering condition correspondence.
- •Compliant to the RoHS directive (2011/65/EU).





FPCAP




Specifications

| Item | Performance Characteristics | | | | |
|---------------------------------------|--|---|--|--|--|
| Category Temperature Range | –55 to +105°C | | | | |
| Rated Voltage Range | 16V | | | | |
| Rated Capacitance Range | 820 to 2200µF | | | | |
| Capacitance Tolerance | ±20% at 120Hz, 20°C | | | | |
| Tangent of loss angle (tan δ) | Less than or equal to the specified value at 120Hz, 20°C | | | | |
| ESR (*1) | Less than or equal to the specified value at 100kHz, 20°C | | | | |
| Leakage Current (%2) | Less than or equal to the specified value. After 2 minutes' application of rated voltage at 20°C | | | | |
| | Test condition | 105°C, rated voltage 2000Hrs. | | | |
| | Capacitance change | Within ±20% of initial value before test | | | |
| Endurance | tan δ | 150% or less than the initial specified value | | | |
| | ESR(**1) | 150% or less than the initial specified value | | | |
| | Leakage current (**2) | Less than or equal to the initial specified value | | | |

*1 ESR should be measured at both of the terminal ends closest to the capacitor body.

*2 Conditioning : If any doubt arises, measure the leakage current after the voltage treatment of applying DC rated voltage continuously to the capacitor for 120 minutes at 105°C.

Dimensions




| | | | (mm) |
|---------|-----|-----|------|
| φD×L | φd | Р | α |
| φ8×20L | 0.6 | 3.5 | 1.5 |
| φ10×20L | 0.6 | 5.0 | 1.5 |


Frequency coefficient of rated ripple current

| Frequency | 120 Hz | 1 kHz | 10 kHz | 100 kHz | 300 kHz |
|-------------|--------|-------|--------|---------|---------|
| Coefficient | 0.10 | 0.45 | 0.50 | 1.00 | 1.00 |

Type numbering system (Example : 16V 2200µF) Nichicon part number



FPCAP part number




CONDUCTIVE POLYMER ALUMINUM SOLID ELECTROLYTIC CAPACITORS

RNL ■ Standard Ratings

| Rated Voltage (V) | Surge Voltage (V) | Rated Capacitance (µF) | Case Size ¢D×L (mm) | tan δ | Leakage Current (µA, 2min.) | ESR (mΩ, 100kHz) | Rated Ripple Current (mArms) | NICHICON | FPCAP |
|----------------------|-------------------------|------------------------------|------------------------|-------|-----------------------------------|---------------------|------------------------------------|-----------------|-----------------|
| 16 (1C) 18.4 | | 820 | 8×20 | 0.12 | 1312 | 8 | 7500 | RNL1C821MDS1 | FP-016RE821M-NL |
| | | 1000 | 8×20 | 0.12 | 1600 | 8 | 7500 | RNL1C102MDS1 | FP-016RE102M-NL |
| | 1200 | 8×20 | 0.12 | 1920 | 8 | 7500 | RNL1C122MDS1 | FP-016RE122M-NL | |
| | | 1500 | 10×20 | 0.12 | 2400 | 8 | 8100 | RNL1C152MDS1 | FP-016RE152M-NL |
| | | 1800 | 10×20 | 0.12 | 2880 | 8 | 8100 | RNL1C182MDS1 | FP-016RE182M-NL |
| | | 2200 | 10×20 | 0.12 | 3520 | 8 | 8100 | RNL1C222MDS1 | FP-016RE222M-NL |

Frequency Characteristics (The frequency characteristics are typical and not a guaranteed value.)



• Taping specifications are given in page 26, 27.

• Please refer to page 3 for the minimum order quantity.