## FME Plug to TNC Plug

# multicomp PRO

### RoHS Compliant




#### **Specifications**

Frequency Range Nominal Impedance Bodies Centre Contact Insulation Operating Temperature Range

- : DC-900 MHz
- : 50Ω
- : Brass per JIS-C3604
- : Beryllium copper per ASTM B196 UNS C17300
- : PTFE Per ASTM D1457 and ASTM D1710
- : -55°C to +125°C

#### Diagram



No.	Description	Material	Finish	Qty.
1	Shell	Brass	Nickel 100µ″ Min.	
2	Insulation	PTFE	None	
3	Gasket	Silicone	Red	
4	Body	Brass	Nickel 100µ″ Min.	1
5	Washer		None	
6	Insulation	PTFE		
7	Centre Contact	Brass	Gold	

### Part Number Table

Description	Part Number
FME Plug to TNC Plug	MP-R23-012-00-002611000

#### Dimensions : Millimetres (Inches)

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

