

Resisto fixed output

Resisto 1500 IP66 7600lm 840

0010244



Product features

- Resisto, integrated LED weatherproof luminaire, with UV stabilized flat diffuser designed to achieve uniform lit appearance, optimise light output and to reduce glare. 301 stainless steel diffuser clips and fixing brackets for surface mounting. Polycarbonate housing and diffuser - no yellow discolouration over time. 7600lm; 55W; 138lm/W; 4000K; SDCM<5; non dimmable; CRI80; IP66; IK08; Class I; 69,000hrs (L80B20) lifespan; 1500mm x 89mm x 88mm; D-mark.



PRODUCT OVERVIEW

Product name	Resisto 1500 IP66 7600lm 840
Technology	LED
Housing	PC Polycarbonate
General application	Logistics & Industry
ETIM Class	EC002892
E-number FI	4357057
Warranty	5 years
Fixture luminous flux (lm)	7600
Luminaire efficacy (lm/W)	138
Colour temperature (K)	4000
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM5
Colour Consistency (SDCM)	5
Beam Angle (°)	110
Glare control	< 25
Photobiological Risk Group	RG1
Total power consumption (W)	55
Electrical protection	Class I
Dimmable	No
Dimming method	N/A
LED Flickering Rate	Ultra low (5% or less)
Housing colour	Grey
IP rating	IP66
IK rating	IK08
Product EAN number	5410288102443

DATA TABLE

General data

Product name	Resisto 1500 IP66 7600lm 840
Technology	LED
Housing	PC Polycarbonate
General application	Logistics & Industry
Operating temperature range (°C)	-20°C...+40°C

Resisto fixed output

Resisto 1500 IP66 7600lm 840
0010244

Performance ambient temperature Tq (°C)	25
ETIM Class	EC002892
E-number FI	4357057
Warranty	5 years

Optical data

Fixture luminous flux (lm)	7600
Luminaire efficacy (lm/W)	138
Colour temperature (K)	4000
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM5
Colour Consistency (SDCM)	5
Beam Angle (°)	110
Distribution type	Diffuse
Glare control	< 25
Photobiological Risk Group	RG1

Electrical data

Total power consumption (W)	55
Mains voltage (V)	220-240V
Lamp power factor	1
THD (at 230 V, 50 Hz, full load, at 100% dimming level) xx.x %	20
Electrical protection	Class I
No. Of switching cycles before premature failures	>50000
Dimmable	No
Dimming method	N/A
Drive current (mA)	350
Inrush Current (A)	16
Inrush Duration (µs)	40
Glow Wire Test (°C)	850
Energy Efficiency Class (A->G) of contained light source	D, D(more than 1 Light Source)
Nominal Frequency (Hz)	50/60Hz
LED Flickering Rate	Ultra low (5% or less)
Max. Luminaires per 10A C Breaker	24
Max. Luminaires per 13A C Breaker	32
Max. Luminaires per 16A C Breaker	39
Max. Luminaires per 20A C Breaker	49
Max. Luminaires per 10A B Breaker	24
Max. Luminaires per 13A B Breaker	32
Max. Luminaires per 16A B Breaker	39
Max. Luminaires per 20A B Breaker	49

Lifetime data

Lifespan L70 B50	100000
Lifespan L80 B20	69000
Lifespan L90 B10	31000

Resisto fixed output

Resisto 1500 IP66 7600lm 840
0010244

Physical data

Housing colour	Grey
IP rating	IP66
IK rating	IK08
Diffuser finish	Frosted
Diffuser material	PC Polycarbonate
Nominal Product Length (mm)	1500
Nominal Product Width (mm)	87
Nominal Product Height (mm)	80
Weight (kg)	1.72


Packaging

Single packaging type	Carton
Product EAN number	5410288102443
Packaging single length / height (cm)	150.5
Packaging single width (cm)	10.0
Packaging single depth (cm)	8.5
DUN14 (outer)	15410288102440
Units per outer package	1
Packaging outer length / height (cm)	150.5
Packaging outer width (cm)	10.0
Packaging outer depth (cm)	8.5

Safety data

Optimal operating condition (°C)	-20-40
----------------------------------	--------

PHOTOMETRY



Distance [m]	Cone diameter [m]	Beam diameter [m]	Beam diameter [ft]	Illuminance [lx]
0.5	1.39 1.25	0.54 0.51	1.74 1.67	10137 1016 1234
1.0	2.77 2.51	1.08 1.02	3.48 3.34	2534 254 308
1.5	4.16 3.76	1.62 1.53	5.28 5.00	1138 113 137
2.0	5.55 5.01	2.16 2.04	7.07 6.64	524 83 77
2.5	6.93 6.26	2.70 2.55	8.86 8.31	405 41 46
3.0	8.32 7.52	3.24 3.06	10.65 9.98	282 28 34

Distance [m] Cone diameter [m] Illuminance [lx]
 C0 - C180 (Half beam angle: 108.4°)
 C90 - C270 (Half beam angle: 108.4°)

TECHNICAL DRAWINGS

Resisto fixed output

Resisto 1500 IP66 7600Im 840

0010244

