

## Solid carbide torus milling cutter

2 blades, ULTRA N-coated

**ATORN**<sup>®</sup>



### Application

Torus milling cutter, standard version for machining non-ferrous metals.

### Version

- Solid carbide ultra-fine grain
- Straight shank in accordance with DIN 6535 HA
- Defined edge rounding of the blade
- Centre cutting
- With clearance
- ZrCN ULTRA N-coated
- Radius tolerance = +/- 0.01 mm

Application	Steel (N/mm <sup>2</sup> )			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
							425	190	250	175	210	350							

<b>Art. no.</b>	<b>16653 145</b>
<b>Cutting material</b>	VHM
<b>Surface</b>	ULTRA N
<b>Type</b>	W
<b>Number of cutting edges</b>	2 PCS
<b>Twist angle</b>	30°
<b>Tool holding device</b>	HA parallel shank
<b>Overall length</b>	Normal
<b>Cutting edge diameter</b>	8 mm
<b>Cutting edge length</b>	9 mm
<b>Clearance length</b>	27 mm
<b>Length</b>	63 mm
<b>Clearance diameter</b>	7.7 mm
<b>Shaft diameter</b>	8 mm
<b>Edge radius</b>	2 mm
<b>fz aluminium</b>	0.11 mm

### EAN-Code

4050293342130