

## Articulated hook wrenches

industrial version



### Execution:

- Special steel
- Rounded edges
- With suspension hole
- Extended hook and shank
- Reinforced rivet
- With spring washer
- Surface annealed in burnished finish

### Advantage:

- Longer shank for greater transferable torque
- Reinforced rivet for longer service life with greater force transmission
- Even movement with additional spring washer
- One-hand operation possible
- Excellent material strength with low-tension microstructure



<b>Art. no.</b>	<b>52104 050</b>
<b>Brand</b>	AMF
<b>Manufacturer Part Number</b>	51680
<b>Suitable for nut type</b>	Slotted nut DIN 1804, Bearing nut DIN 981
<b>Suitable for min./max. nut male thread size</b>	155-230 mm
<b>Thickness</b>	8 mm
<b>Length</b>	460 mm
<b>Gross Weight</b>	1.200 kg
<b>Product Group</b>	532

### EAN

4020772051686