

## PCLN clamp holder with internal cooling, negative

For facing and longitudinal turning using CN indexable inserts

**ATORN**<sup>®</sup>

### Application

for longitudinal and face turning with CN indexable insert, 80°

### Version

- precision-made steel carrier with high-performance cooling system, nickel-plated, hardened, toggle-joint clamping system, type C, attack angle 95°, tip angle 80°, clearance angle 0°

### Advantage

- high-performance cooling channel system with three outlets ensures an extremely long service life and reliable working
- Universal use for face and longitudinal turning with large feed depths and unfavourable conditions
- Negative geometry of the body ensures good stability and force absorption at large cutting depths
- Broad range of use: suitable for both finishing and roughing operations



<b>Art. no.</b>	<b>17837 720</b>
<b>ISO name</b>	PCLN R/L 2020 K12 IK G1/8
<b>Shaft height</b>	20 mm
<b>Shank width</b>	20 mm
<b>Length</b>	125 mm
<b>Length of head</b>	28 mm
<b>Programming size</b>	25 mm
<b>Suitable for indexable inserts</b>	CN.. 1204..
<b>Tool design</b>	Left
<b>DIN</b>	4983

### EAN-Code

4050293565959