


PRODUCT SPECIFICATION

Brand	C.K
Product Range	Tin Snips
Catalogue number	4536 & 4537
Date	30/03/2010

<p>Range Description</p> <ul style="list-style-type: none"> Tin Snips 		 <p style="text-align: center;"><i>Straight</i></p> <p style="text-align: center;"><i>Left</i></p> <p style="text-align: center;"><i>Right</i></p>		
<p>Features</p> <p>4536</p> <ul style="list-style-type: none"> Drop forged for strength and durability Hardened and tempered jaws for high cutting performance Screw and bolt assembly for simple re-adjustment PVC coated handles for grip and comfort Fold away spring for convenience Stop pin to prevent finger nipping <p>4537</p> <ul style="list-style-type: none"> Drop forged Chrome molybdenum steel jaws for strength and durability Hardened and tempered jaws for high cutting performance Compound action for reduced effort cutting Versatile – cuts straight, left, and right hand Ideal for cutting Titanium and Stainless steel Ergonomic grips with slip guards for safety 				
Item Number	Item Description	EAN No	Commodity code	Carton Qty
T4536 08	Tin Snips 200mm	5013969579000	82033000	3
T4536 10	Tin Snips 250mm	5013969579109	82033000	3
T4537AS	Compound action snips Straight 250mm	5013969027372	82033000	3
T4537AL	Compound action snips Left 250mm	5013969027358	82033000	3
T4537AR	Compound action snips Right 250mm	5013969027365	82033000	3

Technical product information	
Standards compliance	Non applicable
User health and safety information	None applicable
RoHS/WEEE compliance	These product ranges do not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K tools are guaranteed for life against imperfect materials or workmanship Damage caused through inappropriate use is not covered
Country of origin	4536 – Germany 4537 – Taiwan

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T4536 08	42	13	205	300	60	25	250	314
T4536 10	50	25	250	524	60	25	300	538
T4537AS	67	30	265	389	67	30	265	405
T4537AL	85	20	250	382	85	20	250	402
T4537AR	85	20	250	382	85	20	250	402

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T4536 08	100	300	65	1010		
T4536 10	100	300	65	1696		
T4537AS	90	280	95	1314		
T4537AL	90	280	95	1305		
T4537AR	90	280	95	1305		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T4536 08	14	Hanger					68	Box

T4536 10	14	Hanger					82	Box
T4537AS	1	Sleeve	15	Backing card			100	Box
T4537AL	1	Sleeve	15	Backing card			100	Box
T4537AR	1	Sleeve	15	Backing card			100	Box