



GE
Lighting



PAR 64

FFR 120V

13228

Product information

PAR lamps provide a robust and flexible design solution for a wide range of applications. Choice of PAR36, PAR46, PAR56 or PAR64

- 3000 K or 4200 K colour temperature
 - Choice of beam widths
 - Excellent colour rendering
 - High efficiency combined with low operating costs
 - Robust and reliable
 - UV control
 - Easy retrofit
 - Colour consistent throughout life
 - Colour blends with halogen and fluorescent
-



Product data

EAN Code	0043168132282
DUN Code	00043168132282
Bulb Shape	PAR
Bulb Diameter [mm]	203.2
Cap/Base	G16d
Nominal beam angle [°]	21
Gross weight per piece [g]	1050
Maximum Overall Length [mm]	152.4
Net weight per piece [g]	945
Brand	General Electric (GE)

Performance data

Nominal power [W]	1000
Nominal lamp voltage [V]	120
Nominal lumens [lm]	28000
Nominal correlated colour temperature (CCT) [K]	3200
Colour Rendering Index (CRI) [Ra]	100
Rated Life [h]	800
Ballast Required	Yes
Nominal center beam candlepower (CBCP) [cd]	125000
Coil type	CC-6
Energy efficiency class (EEC)	E
Weighted energy consumption [kWh/1000h]	1083.58

Logistic data

Pack Quantity	6
Pallet quantity UK (PC)	252
Outer case size	197 x 354 x 551 (mm)
Layer quantity	1 UK
Layer quantity UK	1
Product status	Available

Application areas



Club and Disco

Downloads & Links

[Go to the catalog site \(HTTP\)](#)

[Entertainment Solution Spectrum Catalogue \(PDF\)](#)

[Lighting design tools & calculators \(HTTP\)](#)

Disclaimer

Special purpose lamp – Stage Studio. Not suitable for household illumination.