

Thermal device circuit breaker - TCP 10/20A



1324401

<https://www.phoenixcontact.com/gb/products/1324401>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

Thermal miniature circuit breaker, can be plugged into PT 10-FSI/C Push-in fuse terminal block.



Your advantages

- Fast, replacement part-free recommissioning after an event with the reconnection options
- Easy to retrofit in existing systems with vehicle flat-type fuses with identical pin connector pattern
- System disconnection for maintenance actions via the integrated device switch

Commercial Data

Item number	1324401
Packing unit	18 pc
Minimum order quantity	1 pc
Sales Key	CLA111
Product Key	CLA111
GTIN	4063151614812
Weight per Piece (including packing)	13.211 g
Weight per Piece (excluding packing)	13.211 g
Customs tariff number	85362010
Country of origin	ID

Thermal device circuit breaker - TCP 10/20A



1324401

<https://www.phoenixcontact.com/gb/products/1324401>

Technical Data

Product properties

Type	Male
Product type	Thermal device circuit breakers
Number of positions	1

Insulation characteristics

Overvoltage category	II (Installation area)
	III (Actuation area)
Degree of pollution	2

Electrical properties

Fuse type	Automatic device
Fuse	Slow-blow

General

Rated voltage	250 V AC
	72 V DC
	250 V (UL/CSA)
	72 V (UL/CSA)
Rated current I_N	20 A
Rated surge voltage	2.5 kV
Insulation resistance R_{iso}	> 100 M Ω (500 V DC)
Tripping method	T (thermal)
Device resistance	0 Ω
Rated short-circuit switching capacity I_{cn}	200 A (250 V AC)
	200 A (72 V DC)
Short-circuit switching capacity	2000 A (250 V AC / UL 1077)
	2000 A (72 V DC / UL 1077)
Dielectric strength	3000 V AC (Actuation area)
	1500 V AC (Installation area)
Switching cycles, max.	6000 (At 1 x I_n , low-induction)
	3000 (At 1 x I_n , inductive)
	40 (at 6 x I_n , AC)

Dimensions

Width	8.2 mm
Height	24.4 mm
Height NS 35/7,5	55 mm
Depth	44.5 mm

Material specifications

Color	black
-------	-------

Thermal device circuit breaker - TCP 10/20A



1324401

<https://www.phoenixcontact.com/gb/products/1324401>

Flammability rating according to UL 94	V-0
Insulating material group	IIIb
Insulating material	PPS

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP40 (Actuation area)
	IP00 (Connection area)
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 4000 m (amsl (above mean sea level))
Humidity test	240 h, 95 % RH, 40 °C
Shock (operation)	25g (11 ms period, half-sine shock pulse, according to IEC 60068-2-27)
Vibration (operation)	± 0.38 mm (10 ... 57 Hz)
	5g (57 ... 500 Hz)

Standards and regulations

Standards/specifications	EN 60934
--------------------------	----------

Mounting

Mounting type	on base element
---------------	-----------------

Thermal device circuit breaker - TCP 10/20A



1324401

<https://www.phoenixcontact.com/gb/products/1324401>

Approvals



cUL Recognized



UL Recognized



VDE Zeichengenehmigung

cULus Recognized

Thermal device circuit breaker - TCP 10/20A



1324401

<https://www.phoenixcontact.com/gb/products/1324401>

Classifications

ECLASS

ECLASS-9.0	27141116
ECLASS-10.0.1	27141116
ECLASS-11.0	27141116

ETIM

ETIM 8.0	EC000899
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Thermal device circuit breaker - TCP 10/20A

1324401

<https://www.phoenixcontact.com/gb/products/1324401>

Mandatory Accessories

Fuse modular terminal block

Fuse modular terminal block - PT 10-FSI/C - 1088498

<https://www.phoenixcontact.com/gb/products/1088498>



Fuse modular terminal block, fuse type: Flat, fuse type: C, nom. voltage: 400 V, nominal current: 30 A, connection method: Push-in connection, 1 level, Rated cross section: 10 mm², cross section: 0.5 mm²- 16 mm², mounting type: NS 35/7,5, NS 35/15, color: black

Accessories

Flat zack marker sheet

Flat zack marker sheet - ZBFM 5/WH:UNBEDRUCKT - 0803595

<https://www.phoenixcontact.com/gb/products/0803595>



Flat zack marker sheet, Sheet, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, PLOTMARK, mounting type: snapped, for terminal block width: 5.2 mm, lettering field size: 5 x 4.5 mm, Number of individual labels: 120

Thermal device circuit breaker - TCP 10/20A



1324401


<https://www.phoenixcontact.com/gb/products/1324401>

Flat zack marker sheet

Flat zack marker sheet - ZBFM 5/OG:UNBEDRUCKT - 0807180

<https://www.phoenixcontact.com/gb/products/0807180>

Flat zack marker sheet, Sheet, orange, unlabeled, can be labeled with: CMS-P1-PLOTTER, PLOTMARK, mounting type: snap in, for terminal block width: 5.2 mm, lettering field size: 5 x 4.5 mm, Number of individual labels: 120



Phoenix Contact 2022 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

info@phoenixcontact.co.uk