



SCALANCE XC216-4C G (E/IP) managed Layer 2 IE switch; IEC 62443-4-2 certified; Full Gigabit; 12x 10/100/1000 Mbps RJ45 ports; 4x 1000 Mbps combo ports (either 1000 Mbps/ SFPs or 10/100/1000 Mbps RJ45 ports can be used); 1x console port; diagnostics LED; redundant power supply; temp. range -40 °C to +70 °C; mounting: DIN rail/S7 mounting rail/wall; redundancy functions; Office features (RSTP, VLAN,...); PROFINET IO device; Ethernet/IP-compliant; C-plug slot; Default EtherNet/IP

<b>product type designation</b>	<b>SCALANCE XC216-4C G (E/IP def.)</b>
<b>transfer rate</b>	
transfer rate	10 Mbit/s, 100 Mbit/s, 1000 Mbit/s
<b>interfaces / for communication / integrated</b>	
number of electrical connections • for network components or terminal equipment	16; RJ45
number of 10/100/1000 Mbit/s RJ45 ports / integrated	16
number of combo ports / with RJ45 interface for optical plug-in transceiver	4; 1000 MBit/s SFPs
<b>interfaces / for communication / plug-in</b>	
number of electrical connections • for SFP	4; 1000 Mbit/s SFP plug-in transceiver or 100 Mbit/s via SCALANCE SFP991-1(LD) A
<b>interfaces / other</b>	
number of electrical connections • for operator console • for signaling contact • for power supply	1 1 1
type of electrical connection • for operator console • for signaling contact • for power supply	RJ11 2-pole terminal block 3-pole terminal block, permanently installed
design of the removable storage • C-PLUG	Yes
<b>signal inputs/outputs</b>	
operating voltage / of the signaling contacts • at DC / rated value	24 V
<b>supply voltage, current consumption, power loss</b>	
product component / connection for redundant voltage supply	Yes
<b>type of voltage / 1 / of the supply voltage</b> • supply voltage / 1 / rated value • power loss [W] / 1 / rated value • consumed current / 1 / at rated supply voltage / maximum • supply voltage / 1 / rated value • type of electrical connection / 1 / for power supply • product component / 1 / fusing at power supply input • fuse protection type / 1 / at input for supply voltage	DC 24 V 13.2 W 0.55 A 9.6 ... 31.2 V 3-pole terminal block, permanently installed Yes 3.15 A / 125 V
<b>ambient conditions</b>	

ambient temperature	
<ul style="list-style-type: none"> <li>during operation</li> <li>during storage</li> <li>during transport</li> </ul>	<p>-40 ... +70 °C</p> <p>-40 ... +85 °C</p> <p>-40 ... +85 °C</p>
relative humidity	
<ul style="list-style-type: none"> <li>at 25 °C / without condensation / during operation / maximum</li> </ul>	95 %
protection class IP	IP20
<b>design, dimensions and weights</b>	
design	compact
width	140 mm
height	150 mm
depth	125 mm
net weight	1.2 kg
material / of the enclosure	Polycarbonate (PC-GF10) / pressure die cast aluminum
fastening method	
<ul style="list-style-type: none"> <li>35 mm top hat DIN rail mounting</li> <li>wall mounting</li> <li>S7-300 rail mounting</li> <li>S7-1500 rail mounting</li> </ul>	<p>Yes</p> <p>No</p> <p>Yes</p> <p>Yes</p>
<b>product features, product functions, product components / general</b>	
cascading in the case of a redundant ring / at reconfiguration time of <math>\leq 0.3\text{ s}</math>	50
cascading in cases of star topology	any (depending only on signal propagation time)
product function / QoS according to DSCP	Yes
product feature	
<ul style="list-style-type: none"> <li>Cut Through switching method</li> <li>Store &amp; Forward switching method</li> </ul>	<p>No</p> <p>Yes</p>
<b>product functions / management, configuration, engineering</b>	
product function	
<ul style="list-style-type: none"> <li>CLI</li> <li>web-based management</li> <li>MIB support</li> <li>TRAPs via email</li> <li>configuration with STEP 7</li> <li>RMON</li> <li>SMTP server</li> <li>port mirroring</li> <li>multiport mirroring</li> <li>CoS</li> <li>PROFINET IO diagnosis</li> </ul>	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>No</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p>
PROFINET conformity class	B
network load class / according to PROFINET	3
product function / switch-managed	Yes
telegram length / for Ethernet / maximum	10240 byte
protocol / is supported	
<ul style="list-style-type: none"> <li>Telnet</li> <li>HTTP</li> <li>HTTPS</li> <li>TFTP</li> <li>BOOTP</li> <li>GMRP</li> <li>DCP</li> <li>LLDP</li> <li>EtherNet/IP</li> <li>SNMP v1</li> <li>SNMP v2</li> <li>SNMP v3</li> <li>IGMP (snooping/querier)</li> </ul>	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>No</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p>
identification & maintenance function	

<ul style="list-style-type: none"> <li>• I&amp;M0 - device-specific information</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• I&amp;M1 – higher level designation/location designation</li> </ul>	Yes
<b>product functions / diagnostics</b>	
product function	
<ul style="list-style-type: none"> <li>• port diagnostics</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• statistics Packet Size</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• statistics packet type</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• error statistics</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• SysLog</li> </ul>	Yes
<b>product functions / VLAN</b>	
product function	
<ul style="list-style-type: none"> <li>• VLAN - port based</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• VLAN - protocol-based</li> </ul>	No
<ul style="list-style-type: none"> <li>• VLAN - IP-based</li> </ul>	No
number of VLANs / maximum	257
number of VLANs - dynamic / maximum	257
number of VLANs / at ring redundancy (HRP; MRP; standby link)	35
protocol / is supported / GVRP	Yes
<b>product functions / DHCP</b>	
product function	
<ul style="list-style-type: none"> <li>• DHCP server</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• DHCP client</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• DHCP Option 82</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• DHCP Option 66</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• DHCP Option 67</li> </ul>	Yes
<b>product functions / redundancy</b>	
product function	
<ul style="list-style-type: none"> <li>• of the PROFINET IO device / is supported / PROFINET system redundancy</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• ring redundancy</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• High Speed Redundancy Protocol (HRP)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• high speed redundancy protocol (HRP) with redundancy manager</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• high speed redundancy protocol (HRP) with standby redundancy</li> </ul>	Yes
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
<ul style="list-style-type: none"> <li>• media redundancy protocol (MRP) with redundancy manager</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Media Redundancy Protocol Interconnection (MRP-I)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• of the PROFINET IO device / is supported / H-Sync forwarding</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• redundancy procedure STP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• redundancy procedure RSTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• redundancy procedure RSTP+</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• redundancy procedure MSTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Parallel Redundancy Protocol (PRP)/operation in the PRP-network</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)</li> </ul>	No
<ul style="list-style-type: none"> <li>• passive listening</li> </ul>	Yes
protocol / is supported	
<ul style="list-style-type: none"> <li>• LACP</li> </ul>	Yes
<b>product functions / security</b>	
product function	
<ul style="list-style-type: none"> <li>• IEEE 802.1x (radius)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• broadcast/multicast/unicast limiter</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• broadcast blocking</li> </ul>	Yes
protocol / is supported	

• SSH	Yes
• SSL	Yes
<b>product functions / time</b>	
product function	
• SICLOCK support	Yes
• NTP-client	Yes
• SNTP client	Yes
protocol / is supported	
• NTP	Yes
• SNTP	Yes
<b>system modification during operation</b>	
product function / configuration in RUN via CiR/H-CiR	Yes
<b>standards, specifications, approvals</b>	
IT security for industrial automation systems / according to IEC 62443-4-2:2019	Yes
MTBF	46 y
reference code	
• according to IEC 81346-2	KF
• according to IEC 81346-2:2019	KFE
<b>standards, specifications, approvals / CE</b>	
certificate of suitability / CE marking	Yes
product conformity / according to EMC-guideline	2014/30/EU
standard	
• for EMC interference emission	EN 61000-6-4, EN 50121-15
• for immunity to EMC	EN 61000-6-2, EN 50121-4
certificate of suitability / RoHS conformity	Yes; 2011/65/EU
<b>standards, specifications, approvals / hazardous environments</b>	
certificate of suitability	
• CCC / for hazardous zone according to GB standard	Yes
<b>accessories</b>	
product extension / optional / C-PLUG	Yes
<b>further information / internet-Links</b>	
Internet-Link	
• to web page: selection aid TIA Selection Tool	<a href="http://www.siemens.com/tia-selection-tool">http://www.siemens.com/tia-selection-tool</a>
<b>last modified:</b>	2/8/2022 