

## MIRO 12.4 230V-2U OUTPUT RELAY


IN: 230 VAC/DC - OUT: 250 VAC/DC / 6 A

230 V AC/DC  
Screw terminals




When the max. switching voltage/current is exceeded the gold plating is destroyed. The relay will then take on the properties of an output type.

### [Link to Product](#)

#### Illustration



stay connected



Product may differ from Image

### Approvals



### Utilization category

AC-12	6 A (24/110/230 V AC)
AC-15	3 A (24/110/230 V AC)

DC-13 1 A (24 V DC); 0.2 A (110 V DC); 0.1 A (230 V DC)

**Input**

Connection voltage - current 230 VAC/DC (195...253 VAC/DC) - 5mA

LED display LED (green)

**General data**

Mech./ elect. life 20.000.000 switching cycles/load dependent

Test isolation voltage 4 kV; safe separation (EN 60947-1)

Mounting method DIN-rail mountable (EN 60715)

Temperature range -20...+55 °C

Dimensions H x W x D 90x12.4x65 mm

**Output**

Switching voltage max. 250 V AC/DC

Switching current per output max. 6 A

Min. load current 10 mA (12 V DC)

Power rating (voltage dependent) max. 1500 VA/120 W

Switching frequency max. 10 Hz

Contact material Ag Sn O<sub>2</sub>

Energize/release/contact bounce time 10/15/1.5 ms

**Commercial data**

country of origin CZ

customs tariff number 85364900

minimum order quantity 1