

FEEDER LEFH -HAND SIDE, CONNECTION MAIN
CIRCUIT: INPUT: SCREW, OUTPUT: SPRING 3 SLOT
FOR COMPACT LOAD FEEDER TERMINAL MAX. 25
MM2 / 35 MM2

General technical data:

product brand name		SIRIUS
Product designation		infeed left
Protection class IP		IP20
Degree of pollution		3
Number of slots for compact feeder		3
Installation altitude at height above sea level maximum	m	2 000
Ambient temperature		
• during transport	°C	-55 ... +80
• during storage	°C	-55 ... +80
• during operation	°C	-20 ... +60
Vibration resistance		f = 4 to 5.8 Hz; d = 15 mm; f = 5.8 to 500 Hz; a = 2 m / s ² 10 cycles
Shock resistance		Semi-sinusoidal a = 6 m/s ² at 10 ms; 3 pos. and 3 neg. Shock in all axes
Equipment marking acc. to DIN EN 61346-2		W
Equipment marking acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750		W

Main circuit:

Operating current with AC at 400 V Rated value	A	63
Operating voltage at AC-3 Rated value maximum	V	690

Installation/ mounting/ dimensions:

Mounting type		screw and snap-on mounting
Width	mm	180

Height	mm	208
Depth	mm	144
Connections/ Terminals:		
Type of electrical connection for main current circuit		spring-loaded terminals
Wire stripping length for main contacts	mm	13
Connectable conductor cross-section for supply for main contacts using the upper clamping point		
• solid	mm ²	2.5 ... 35
• stranded	mm ²	2.5 ... 35
• finely stranded with core end processing	mm ²	2.5 ... 25
• finely stranded without core end processing	mm ²	2.5 ... 25
Connectable conductor cross-section for supply for main contacts using the lower clamping point		
• solid	mm ²	2.5 ... 35
• stranded	mm ²	2.5 ... 35
• finely stranded with core end processing	mm ²	2.5 ... 25
• finely stranded without core end processing	mm ²	2.5 ... 25
Connectable conductor cross-section for supply for main contacts using both clamping points		
• solid	mm ²	2 ... 25
• stranded	mm ²	2 ... 25
• finely stranded with core end processing	mm ²	2 ... 16
• finely stranded without core end processing	mm ²	2 ... 16
AWG number as coded connectable conductor cross section for supply for main contacts		
• using the upper clamping point		12 ... 2
• using the lower clamping point		12 ... 2
• using both clamping points		16 ... 2
Type of connectable conductor cross-section for supply for main contacts using the upper clamping point		
• solid		2.5 ... 35 mm ²
• stranded		2.5 ... 35 mm ²
• finely stranded with core end processing		2.5 ... 25 mm ²
• finely stranded without core end processing		2.5 ... 25 mm ²
Type of connectable conductor cross-section for supply for main contacts using the lower clamping point		
• solid		2.5 ... 35 mm ²
• stranded		2.5 ... 35 mm ²
• finely stranded with core end processing		2.5 ... 25 mm ²
• finely stranded without core end processing		2,5 ... 25 mm ²

Type of connectable conductor cross-section for supply for main contacts using both clamping points		
<ul style="list-style-type: none"> • solid • stranded • finely stranded with core end processing • finely stranded without core end processing 		<p>2 x (2.5 ... 25 mm²)</p> <p>2 x (2.5 ... 25 mm²)</p> <p>2 x (2.5 ... 16 mm²)</p> <p>2 x (2.5 ... 16 mm²)</p>
Type of connectable conductor cross-section for AWG conductors for supply for main contacts		
<ul style="list-style-type: none"> • using the upper clamping point • using the lower clamping point • using both clamping points 		<p>12 ... 2</p> <p>12 ... 2</p> <p>2 x (16 ... 2)</p>
Connectable conductor cross-section for main contacts for load-side outgoing feeder		
<ul style="list-style-type: none"> • solid • stranded • finely stranded with core end processing • finely stranded without core end processing 	<p>mm²</p> <p>mm²</p> <p>mm²</p> <p>mm²</p>	<p>1.5 ... 10</p> <p>1.5 ... 10</p> <p>1.5 ... 6</p> <p>1.5 ... 6</p>
AWG number as coded connectable conductor cross section for main contacts for load-side outgoing feeder		
		14 ... 8
Type of connectable conductor cross-section for main contacts for load-side outgoing feeder		
<ul style="list-style-type: none"> • solid • stranded • finely stranded with core end processing • finely stranded without core end processing 		<p>2x (1.5 ... 6 mm²), 1x (1.5 ... 10 mm²)</p> <p>2x (1.5 ... 6 mm²), 1x (1.5 ... 10 mm²)</p> <p>2 x (1.5 ... 6) mm²</p> <p>2 x (1.5 ... 6) mm²</p>
Type of connectable conductor cross-section for AWG conductors for main contacts for load-side outgoing feeder		
		2 x (16 ... 10), 1 x (16 ... 8)

Certificates/ approvals:

General Product Approval	EMC	Shipping Approval
--------------------------	-----	-------------------



Shipping Approval	other
-------------------	-------



[Declaration of Conformity](#)

[Environmental Confirmations](#)

other

[other](#)

Safety related data:

Protection against electrical shock	finger-safe
-------------------------------------	-------------

Further information


Information- and Downloadcenter (Catalogs, Brochures,...)
<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)
<http://www.siemens.com/industrymall>


Cax online generator
<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA68128AC>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<http://support.automation.siemens.com/WW/view/en/3RA68128AC/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)
<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RA68128AC&lang=en>



last modified:



09.03.2015