

**AC283**



**FLUKE®**

**SureGrip™  
Pincer Clips**

# AC283

FLUKE®

## SureGrip™ Pincer Clips

- 11.5 cm (4.5 in) insulated, flexible shaft
- 0.5 cm (0.20 in) pincer opening
- Pincers made of tempered, nickel plated wire
- Recommended for use with TL222 Test Leads
- Safety: IEC 61010-031 CAT II 1000 V, 1 A
- Pollution Degree 2, 2000 m altitude
- Operating temperature: -20 °C to 55 °C (-4 °F to 131 °F), 90 % RH
- One-year warranty



### **WARNING to avoid possible electrical shock or personal injury:**

- DO NOT USE above maximum ratings.
- Inspect test lead components for damage and check for continuity. DO NOT USE test leads that are damaged, that have the inner contrasting color of the wire exposed, or that show high resistance.
- Make sure test probes are firmly connected to instrument and other accessories.
- When used with accessories or meter, the lowest measurement category rating applies.
- Clean with a soft towel moistened with water and mild detergent. DO NOT IMMERSE in liquid.
- Do not use in wet or damp locations.
- If this product is used in a manner not specified by the instructions, the protection may be impaired.
- For assistance or information on Fluke products call: 800-443-5853 in the USA and Canada, 31-40-2-675-200 in Europe or 425-446-5500 from all other countries; or visit us at our website at [www.fluke.com](http://www.fluke.com).

Explanation of symbols	
	Parts protected throughout by DOUBLE INSULATION or REINFORCED INSULATION
	Risk of danger, refer to this documentation
	Conforms to European Union directives
<b>CAT II</b>	MEASUREMENT CAT II is applicable to test and measuring circuits connected directly to utilization points (socket outlets and similar points) of the low-voltage mains installation.

Fluke Corporation  
 EC Box 9090  
 Everett, WA  
 98206-9090

Fluke Europe BV  
 PQ Box 1186  
 5602 BD Eindhoven,  
 The Netherlands

9/2019



©2019 Fluke Corporation.  
 Specifications subject to change  
 without notice. Printed in USA.  
 Country of origin Taiwan.  
[www.fluke.com](http://www.fluke.com)



EAN 0095969919869