

Spiro drill chuck

Precision design



Application:

For clamping and releasing drill bits quickly without a key.

Execution:

- Permanent and automatic retightening.
- Hardened wear parts.
- Particularly suitable for high rotation speeds on drills and boring mills.
- With internal taper chuck in accordance with DIN 238.

Advantage:

- High concentricity < 0.05 mm.



Art. no.	21305 030
Brand	RÖHM
Manufacturer Part Number	87 1004
Min./max. clamping width	0-6.5 mm
Suitable for taper	B 12
Outer diameter	35 mm
Length closed	68.6 mm
Gross Weight	0.114 kg
Product Group	201

EAN

4019208195124