

ITEM NO./PART CODE : SD-670 DC 100uA / 48-0305

DATE : APR 27, 2017

ELECTRICAL INDICATING METER.

SPECIFICATION :

- | | | |
|------------------------------|---|---|
| 1. MOVEMENT | : | MOVING COIL TYPE |
| 2. MEASURING RANGE | : | 90 DEGREE |
| 3. POINTER | : | 0.4mm |
| 4. POINTER COLOR | : | RED |
| 5. POINTER POSITION | : | LEFT ZERO HAND |
| 6. SCALE | : | ALUMINUM |
| 7. COIL RESISTANCE | : | 1,500 Ω \pm 10% |
| 8. CURRENT SENSITIVITY | : | DC 100uA \pm 2.5% |
| 9. FRICTION TOLERANCE | : | \pm 0.4mm |
| 10. BALANCE | : | WITHIN THE POINTER WIDTH \pm 0.4mm
VERTICALLY AND HORIZONTALLY |
| 11. OVER CURRENT | : | WITHIN 5 ITEMS OF RATE CURRENT |
| 12. OPERATION TEMP. | : | BETWEEN - 20 $^{\circ}$ C AND + 60 $^{\circ}$ C |
| 13. ZERO POSITION DIFFERENCE | : | WITHIN WIDTH OF POINTER |
| 14. + TERMINAL | : | RIGHT SIDE WHEN YOU SEE THE IN FRONT |

