


Ring Terminals

Nylon-Insulated Large Ring Terminals



CAT. NO.	PKG. QTY.	WIRE RANGE	MAX. INS.	BOLT HOLE	REC. TOOL	DIMENSIONS				STOCK THICK.		
						A	B	C	M			
<i>Flex Class 41/24</i>												
RD167	200	8	.340	#8	ERG4007	1.48	.42	.28	1.29	.04		
RD8-10	25	8	.340	#10		1.48	.42	.28	1.29			
RD367	200	8	.340	#10		1.48	.42	.28	1.29			
RD8-14	25	8	.340	¼"		1.54	.46	.36	1.32			
RD717	200	8	.340	¼"		1.54	.46	.36	1.32			
RD8-516	25	8	.340	⅝"		1.63	.57	.36	1.35			
RD727	200	8	.340	⅝"		1.63	.57	.36	1.35			
RD8-38	25	8	.340	¾"		1.63	.57	.36	1.35			
RD737	200	8	.340	¾"		1.63	.57	.36	1.35			
RD8-12*	25	8	.310	½"		TBM6S	1.79	.82	.55		1.39	
RD757*	200	8	.310	½"	1.79		.82	.55	1.39			
RD10161	200	8AN	.270	#8	ERG4007	1.40	.41	.24	1.20	.04		
RD10361	200	8AN	.270	#10		1.40	.41	.24	1.20			
RD10711	200	8AN	.270	¼"		1.45	.45	.27	1.22			
RD10721	200	8AN	.270	⅝"		1.53	.56	.34	1.25			
RD10731	200	8AN	.270	¾"		1.53	.56	.34	1.25			
<i>Flex Class 63/24</i>												
RE6-10	20	6	.420	#10		ERG4007	1.65	.49	.28		1.40	.04
RE267	200	6	.420	#10	1.65		.49	.28	1.40			
RE6-14	20	6	.420	¼"	1.65		.49	.28	1.40			
RE717	200	6	.420	¼"	1.65		.49	.28	1.40			
RE6-516	20	6	.420	⅝"	1.76		.61	.34	1.47			
RE727	200	6	.420	⅝"	1.76		.61	.34	1.47			
RE6-38	20	6	.420	¾"	1.76		.61	.34	1.47			
RE737	200	6	.420	¾"	1.76		.61	.34	1.47			
RE6-12*	20	6	.395	½"	TBM6S		1.83	.82	.55	1.43		
RE757*	200	6	.395	½"			1.83	.82	.55	1.43		
RE10261	200	6AN	.315	#10	ERG4007	1.55	.49	.24	1.31	.04		
RE10711	200	6AN	.315	¼"		1.55	.49	.27	1.31			
RE10721	200	6AN	.315	⅝"		1.70	.60	.34	1.40			
RE10731	200	6AN	.315	¾"		1.70	.60	.34	1.40			
<i>Flex Class 105/24</i>												
RF4-10	15	4	.510	#10	TBM6S	1.76	.56	.36	1.49	.04		
RF267	100	4	.510	#10		1.76	.56	.36	1.49			
RF4-14	15	4	.510	¼"		1.76	.56	.36	1.49			
RF717	100	4	.510	¼"		1.76	.56	.36	1.49			
RF4-516	15	4	.510	⅝"		1.84	.62	.35	1.53			
RF727	100	4	.510	⅝"		1.84	.62	.35	1.53			
RF4-38	15	4	.510	¾"		1.84	.62	.35	1.53			
RF737	100	4	.510	¾"		1.84	.62	.35	1.53			
RF757*	100	4	.500	½"		1.90	.82	.55	1.49			
RF10261	100	4AN	.380	#10		TBM6S	1.78	.55	.30		1.51	.07
RF10711	100	4AN	.380	¼"	1.78		.55	.30	1.51			
RF10721	100	4AN	.380	⅝"	1.80		.62	.34	1.49			
RF10731	100	4AN	.380	¾"	1.80		.62	.34	1.49			
RM737	20	250kcmil	.868	¾"	TBM6S		3.00	1.13	.65	2.51		
RM747	20	250kcmil	.868	⅞"		3.00	1.13	.65	2.51			
RM757	20	250kcmil	.868	1"		3.00	1.13	.65	2.51			
RM9731	20	4/0AN	.750	¾"		3.00	1.13	.66	2.51			
RM9751	20	4/0AN	.750	1"		3.00	1.13	.66	2.51			

CAT. NO.	PKG. QTY.	WIRE RANGE	MAX. INS.	BOLT HOLE	REC. TOOL	DIMENSIONS				STOCK THICK.	
						A	B	C	M		
RG2-10	10	2	.588	#10	TBM6S	2.15	.69	.40	1.83	.05	
RG267	50	2	.588	#10		2.15	.69	.40	1.83		
RG2-14	10	2	.588	¼"		2.15	.69	.40	1.83		
RG717	50	2	.588	¼"		2.15	.69	.40	1.83		
RG2-516	10	2	.588	⅝"		2.15	.69	.40	1.83		
RG727	50	2	.588	⅝"		2.15	.69	.40	1.83		
RG2-38	10	2	.588	¾"		2.15	.69	.40	1.83		
RG737	50	2	.588	¾"		2.15	.69	.40	1.83		
RG2-12	10	2	.588	½"		2.35	.80	.49	1.93		
RG757	50	2	.588	½"		2.35	.80	.49	1.93		
RG9711	50	2AN	.453	¼"	TBM6S	2.07	.69	.40	1.74	.06	
RG9731	50	2AN	.453	⅝"		2.07	.69	.40	1.74		
RG9751	50	2AN	.453	1"		2.26	.80	.49	1.84		
RH717	50	1/0	.629	¼"		2.14	.77	.43	1.81		
RH727	50	1/0	.629	⅝"		2.14	.77	.43	1.81		
RH737	50	1/0	.629	¾"		2.14	.77	.43	1.81		
RH757	50	1/0	.629	1"		2.34	.77	.54	1.90		
RH9711	50	1AN	.500	¼"		2.14	.77	.44	1.81		
RH9731	50	1AN	.500	⅝"		2.14	.77	.44	1.81		
RH9751	50	1AN	.500	1"		2.34	.77	.54	1.90		
RJ717	100	2/0	.675	¼"	TBM6S	2.34	.83	.46	1.96	.06	
RJ727	100	2/0	.675	⅝"		2.34	.83	.46	1.96		
RJ737	100	2/0	.675	¾"		2.34	.83	.46	1.96		
RJ757	100	2/0	.675	1"		2.48	.89	.54	2.03		
RJ9711	50	1/0AN	.550	¼"		2.35	.83	.46	1.97		
RJ9731	50	1/0AN	.550	⅝"		2.35	.83	.46	1.97		
RJ9751	50	1/0AN	.550	1"		2.49	.89	.55	2.04		
RK717	25	3/0	.765	¼"		2.60	.93	.54	2.21		
RK727	25	3/0	.765	⅝"		2.60	.93	.54	2.21		
RK737	25	3/0	.765	¾"		2.60	.93	.54	2.21		
RK9731	100	2/0AN	.610	¾"	2.52	.93	.55	2.14			
RK9751	100	2/0AN	.610	1"	2.60	.93	.55	2.15			
RL737	25	4/0	.785	¾"	TBM6S	2.83	1.04	.57	2.35	.07	
RL757	25	4/0	.785	1"		2.83	1.04	.57	2.35		
RL9731	25	3/0AN	.680	¾"		2.83	1.04	.57	2.36		
RL9751	25	3/0AN	.680	1"		2.83	1.04	.57	2.36		
RM737	20	250kcmil	.868	¾"		TBM6S	3.00	1.13	.65		2.51
RM747	20	250kcmil	.868	⅞"			3.00	1.13	.65		2.51
RM757	20	250kcmil	.868	1"			3.00	1.13	.65		2.51
RM9731	20	4/0AN	.750	¾"			3.00	1.13	.66		2.51
RM9751	20	4/0AN	.750	1"			3.00	1.13	.66		2.51



*Brazeed Seam

AN=Aircraft Wire