

Tool cabinet with 3 vertical pull-outs

For particularly space-saving storage of CNC tools



Execution:

- Robust design made of 3 mm steel sheet
- Sturdy plastic rollers with needle bearings that withstand heavy loads
- Includes tool holders with receptacles for optimum use of space and precise fit
- Access on both sides reduces the injury risk
- Drawers separately lockable and with label field for easy identification
- Lateral fork pockets for quick and easy relocation using a pallet truck or fork lift truck
- Store up to 90 metal cutting tools over a width of 1040 mm
- Variable attachment of tool holders in holes with 25-mm hole spacing
- Other paint colours deliverable on request.

Advantage:

- Clean, secure and careful storage of all common drilling and milling tools
- Optimum visibility and quick access thanks to a unique system with plastic holders
- Maximum load-bearing capacity and steady drawer guidance with revolving wheels



Art. no.	50659 010
Brand	APFEL
Manufacturer Part Number	2336357
Model	WKS 008 set Z
Door design	Full-sheet panel
Number of vertical pull-out mechanisms	3 PCS
Number of holders	9 PCS
Vertical pull-out mechanism design	With tool holder WHK 9 18 for max. 90 tools
Load-carrying capacity per pull-out mechanism	1800 kg
Height	1240 mm
Width	1040 mm
Depth	1050 mm
Load-carrying capacity	5400 kg
Lock type	Cylinder lock
Material	Sheet steel
Cabinet colour	Anthracite grey RAL 7016
Colour of front	Grey white RAL 9002
Gross Weight	450.000 kg
Product Group	586