

MICROWAVE TEST ASSEMBLIES, 3.5mm (male), 3.5mm (male), 50 Ohm, 26.5 GHz, 36in

SF526E/11PC35/11PC35/36in

Properties

- Applicable up to 26.5 GHz
- High phase- and amplitude stability with flexure and movement
- Excellent insertion and return loss
- Precise and repeatable measurements
- Long life time - lower measurement cost



Product configuration

Type of cable	SUCOFLEX_526_E
Type description connector A	SF_11_PC35-510
Series connector A	PC 3.5, straight - plug
Series connector B	PC 3.5, straight - plug
Length	914 mm
	36 inch
Length type	REF to REF

Electrical data

Impedance	50 Ω
Max. operating frequency	26.5 GHz
Min. return loss	16.6 dB
VSWR max	1.35 dB
Max. insertion loss	1.64 dB
Signal delay	4.3 ns/m
Propagation velocity	77 %
Min. screening effectiveness	90 dB
Max. screening frequency	18 GHz
Amplitude stability vs. flexure	+/- 0.1 dB
Phase stability vs. flexure	+/- 8 °

Electrical Data (frequency related)

Frequency range	Return loss	VSWR max
0 GHz ... 18 GHz	19 dB	1.253

MICROWAVE TEST ASSEMBLIES, 3.5mm (male), 3.5mm (male), 50 Ohm, 26.5 GHz, 36in
SF526E/11PC35/11PC35/36in

Mechanical data	
Cable diameter	5.5 mm
Static bending radius	16 mm
Flexing cycles	100000
Environmental data	
Operation temperature	-40 °C ... 85°C
Ordering information	
Item number	Item description
85207924	SF526E/11PC35/11PC35/36in

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P37404 / Date of publication: 16.11.2023 / uncontrolled copy