


FILTERFANS IP 54 98–247 m³/h



PRODUCT	PF 32.000		PF 42.500		PF 43.000			
ARTICLE NO.	●	11632101055	11632801055	11642101055	11642801055	11643101055	11643801055	Unit
ARTICLE NO.	●	11632101050	11632801050	11642101050	11642801050	11643101050	11643801050	


DATA								
Rated voltage ±10 %	AC 50 60 Hz		DC		AC 50 60 Hz		DC	
	230		24		230		24	
Unimpeded airflow	98 108		98		125 138		125	
Airflow rate in combination with exhaust filter	73 80		73		93 102		93	
Power consumption	19 18		5		18 17		4.7	
Current consumption	0.12 0.18		0.21		0.12 0.1		0.2	
Type of connection	terminal strip	cable, 2-core, length 310 mm		spring type terminal				
Temperature range	-40 ... +55 -40 ... +131							°C °F
Service life L ₁₀ (+40 °C)	37500		62500		40000		70000	
Dimensions (X x Y)	202 x 202			252 x 252				
Installation depth (Z2) + Construction height (Z1)	87 + 6		81 + 6		97 + 6		38 + 6	
Cut-out dimensions (W x H)	177 x 177			223 x 223				

ACCESSORIES	ARTICLE NUMBER		Page	
Exhaust filter	●	11730001055	11740001055	40
Exhaust filter	●	11730001050	11740001050	40
Spare filter mats	5 pieces	18611600031	18611600032	41
Thermostat			17121000000	39
Hygrostat			17207000000	39
Rainhood in stainless steel			18102000017	39

For additional models, options and voltages visit www.pfannenberg.com or contact us directly.




Performance curves on page 158–159.



Comprehensive technical documentation such as

- operating instruction, technical data, approvals
- cut-out drawing, CAD | EPLAN | Zuken | WSCAD data

can be retrieved by entering this webcode in the search window on www.pfannenberg.com



FILTERFANS IP 54 480–875 m³/h



PRODUCT	PF 65.000	PF 66.000		PF 67.000			
ARTICLE NO.	●	11665102055	11666102055	11666022055	11667102055	11667022055	Unit
ARTICLE NO.	●	11665102050	11666102050	11666022050	11667102050	11667022050	


DATA						
Rated voltage ±10 %	AC 50 60 Hz					
	230		230		400/460 3 ~	
Unimpeded airflow	480 480		640 653		845 875	
Airflow rate in combination with exhaust filter	370 370		445 445		560 625	
Power consumption	80 100		120 160		120 155	
Current consumption	0.35 0.45		0.53 0.72		0.26 0.25	
Type of connection	spring type terminal					
Temperature range	-40 ... +55 -40 ... +131					
Service life L ₁₀ (+40 °C)	40000					
Dimensions (X x Y)	320 x 320					
Installation depth (Z2) + Construction height (Z1)	150 + 7					
Cut-out dimensions (W x H)	292 x 292					

ACCESSORIES	ARTICLE NUMBER		Page	
Exhaust filter	●	11760002055	40	
Exhaust filter	●	11760002050	40	
Spare filter mats	5 pieces	18611600033	41	
Thermostat			17121000000	39
Hygrostat			17207000000	39
Rainhood in stainless steel			18102000020	39

For additional models, options and voltages visit www.pfannenberg.com or contact us directly.



Performance curves on page 159–160.



Comprehensive technical documentation such as

- operating instruction, technical data, approvals
- cut-out drawing, CAD | EPLAN | Zuken | WSCAD data

can be retrieved by entering this webcode in the search window on www.pfannenberg.com

