

HEATER 110-120 V, 20 W;UL-APP. HGK 047-04701.9-00



Figure similar

Model		
product brand name		SIVACON
General technical data		
Active power consumption / Rated value	W	20
Operating temperature / minimum	°C	-45
Voltage		
Continuous heat output / at 20 °C	W	20
Inrush current / typical	A	1.5
Protection class		
Protection class IP		IP44
Main circuit		
Operating voltage		
• Rated value / minimum	V	120
• Rated value / maximum	V	120
• with AC / at 50 Hz / Rated value / minimum	V	110
• with AC / at 50 Hz / Rated value / maximum	V	110
• with AC / at 60 Hz / Rated value / minimum	V	120
• with AC / at 60 Hz / Rated value / maximum	V	120
Operating current / of the slow-blow fuse link	A	2
Product details		
Product component		
• blower		No
• Thermostat		No

Mechanical Design		
Height	mm	70
Width	mm	50
Depth	mm	25

Environmental conditions		
Relative humidity / Reference value	%	90
<b>Ambient temperature</b>		
• during storage / minimum	°C	-45
• during storage / maximum	°C	70

Certificates		
<b>Equipment marking</b>		
• acc. to DIN EN 61346-2		R
• acc. to DIN EN 81346-2		E

General Product Approval	Declaration of Conformity
--------------------------	---------------------------



### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR21102C>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/8MR21102C/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=8MR21102C](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8MR21102C)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015