Screened Cat 5e, F/UTP, LSZH Cable









Application

A 4 pair high performance cable that consists of twisted pair conductors, used mainly for data transmission. Category 5E supports a frequency range of up to 100MHz and is designed for transmission speeds of up to 1 gigabit per second (Gigabit Ethernet).

Characteristics

Temperature Rating : Fixed: -30°C to +50°C
Minimum Bending Radius : Fixed: 4 × overall diameter

Flexed: 8 × overall diameter

Core Identification : Pair 1: Blue, White/Blue

Pair 2: Orange, White/Orange Pair 3: Green, White/Green Pair 4: Brown, White/Brown

Sheath Colour : Violet

Cable Standards

ISO/IEC 11801, TIA 568C.2, YD/T1019

Construction

Conductor

Class 1 solid copper conductor

Insulation

HDPE (High Density Polyethylene)

Drain Wire

Tinned copper

Screen

Aluminium foil

Sheath

LSZH (Low Smoke Zero Halogen)

This product range is available on reels of 305m or per metre

Dimensions

No. of Pairs (24 AWG) Nominal Diameter Over Insulation mm		Nominal Overall Diameter mm	Nominal Weight kg/305m box	
4	1	5.8	14	

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



Screened Cat 5e, F/UTP, LSZH Cable



Performance Characteristics

Frequency MHz	Attenuation dB	NEXT dB	PS-NEXT dB	RL dB	ELFEXT dB	PSELFEXT dB	Phase Delay ns
1	2	65.3	62.3	20	63.8	60.8	570
4	4.1	56.3	53.3	23	51.8	48.8	552
8	5.8	51.8	48.8	24.5	45.7	42.7	546.73
10	6.5	50.3	47.3	25	43.8	40.8	545.38
16	8.2	47.2	44.4	25	39.7	36.7	543
20	9.3	45.8	42.8	25	37.8	34.8	542.05
25	10.4	44.3	41.3	24.3	35.8	32.8	541.2
31.25	11.7	42.9	39.9	23.6	33.9	30.9	540.44
62.5	17	38.4	35.4	21.5	27.9	24.9	538.55
100	22	35.3	32.3	20.1	23.8	20.8	537.6

Electrical Characteristics at 20°C

Impedance	Maximum Resistance of	Maximum Resistance	
(1-100MHz)	Conductor at 20°C	Unbalance	
Ω	Ω/km	% max.	
100±15	95	5	

Part Number Table

Description	Cable Length	Part Number
Screened Network Cable, Cat 5e, F/UTP, LSZH, 4 Pair, 24AWG, Violet	305m or per metre	PP002140

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

