Solvex® 37-676 37-695



Chemical & Liquid Protection (NBR) Nitrile



High-comfort, chemical resistant glove for range of applications

DESCRIPTION

- Available in a wide selection of lengths, thicknesses, sizes and linings, the Ansell Sol-Vex® nitrile glove is designed to deliver optimal results in wet or dry work environments where chemical resistance is crucial. Fully reusable, with an unequaled abrasion resistance, it provides superb comfort for the wearer.
- unequaled abrasion resistance, it provides superb comfort for the wearer.
 Sol-Vex® nitrile gloves are the ideal choice for safe handling in a wide range of work environments where harsh chemicals are present.
- The cotton-flock liner to the glove, combined with the flexibility of the nitrile film, offer exceptional comfort for the wearer.
- The reversed lozenge finish further enhances levels of grip.
- The sandpatch finish gives the glove a smooth surface that decreases indirect costs thanks to fewer rejects of fragile parts.
- The Sol-Vex® 37-695 glove has a longer length (38 cm) than standard, extending protection further to the wrist and lower forearm area.

PRODUCT DETAILS

Coating material	Nitrile
Liner material	Flocked
Grip design	Reversed lozenge
Cuff style	Gauntlet
Colour	Green
AQL	0.65
EN Sizes	7,8,9,10,11
Length (mm)	37-676: 330 37-695: 380
Packaging	37-676: 12 pairs in a bag; 12 bags in a carton 37-695: 12 pairs in a bag; 6 bags in a carton

Print date 04-09-2018

Ansell Healthcare Europe N.V. (European Head Office) Riverside Business Park, Block J Boulevard International 55, 1070 Brussels, Belgium Tel. +32 (0) 2 528 74 00 • Fax +32 (0) 2 528 74 01 • Fax Customer Service +32 (0) 2 528 74 03 http://www.ansell.eu • E-mail info@ansell.eu






IDEAL APPLICATIONS

- Agrochemicals
- Chemical processing and preparation
- Metal fabrication
- Printing industry
- Refining Oil & Petrol

PRIMARY INDUSTRIES



STANDARDS AND CERTIFICATIONS



Ansell