

Knurling tool (series RD2 model 851)

for knurl pressing on lathes and turning machines



Application:

For knurl forming for knurl profiles in accordance with DIN 82 RAA, RBL30°/45°, RBR30°/45°, RGE 30° and RGE 45° in the steel, stainless steel and non-ferrous metals material groups.

Execution:

- hardened steel tool holder, integrated tip height, HSS runner pin

Advantage:

- Available adapter system guarantees high compatibility
- modular design enables right-handed and left-handed knurl press holder
- Inexpensive knurl production
- flexible centring



Art. no.	19006 021
Brand	ZEUS-ECO
Manufacturer Part Number	31002835
Suitable for knurling size	20 x 8 x 6 mm
Shank width	20 mm
Shaft height	20 mm
For min./max. workpiece diameter	10-120 mm
Gross Weight	0.406 kg
Product Group	1FP