

FR 8, 8 OHM & FR8, 4 OHM




8 cm (3.3") full range speaker with good bass reproduction, balanced frequency response and high efficiency. Especially suitable as built-in speaker for music reproduction and as driver for 100 V network column speakers.

Typical applications:


- Narrow network column speakers
- Control speaker for electronic devices
- Ceiling-mounted speakers in railway carriages and busses
- Electronic musical instruments

Technical Data:		
	FR8, 8 Ohm	FR8, 4 Ohm
Rated power		10 Watt
Maximum power		15 Watt
Nominal impedance	8 Ohm	4 Ohm
Frequency response (-10 dB)		130 - 20000 Hz
Mean sound pressure level		86 dB (1W/1m)
Maximum cone displacement		4 mm
Resonance frequency fs		150 Hz
Magnetic induction		1,4 Tesla
Magnetic flux		200 μ Weber
Height of front pole-plate		3 mm
Voice coil diameter		1,5 cm
Height of winding		0,5 cm
Cutout diameter		7,5 cm
Net weight		0,24 kg
D.C. resistance Rdc		7 Ohm
Mechanical Q factor Qms		1,16
Total Q factor Qts		0,96
Equivalent volume Vas		0,67 l
Effective piston area Sd		30 cm ²
Dynamically moved mass Mms		1,7 g
Force factor Bxl		2,5 T · m
Inductance of the voice coil L		0,62 mH


Frequency and Impedance Response




Radiation Pattern at 2000Hz



Radiation Pattern at 5000 Hz



Radiation Pattern at 10000 Hz



Dimensions

