

Pneumatic straight grinder G 357 H

**MANNESMANN
DEMAG**

Application:

For light deburring work

Advantage:

- Floating bearing ensures scratch-free workpiece processing
- Reduced cutter wear and tool life extension - tooth breakage is avoided

Delivery:

Includes hose unit and collet chuck keys



Art. no.	75061 090
Model	G 357 H
Valve design	Lever valve
Max. idle speed	38000 rpm
Min./max. idle speed	0-38000 rpm
Power output	320 W
Air consumption	7.5 l/s
Connection thread	G 1/4 inch
Sound-pressure level	73 dB
Length	170 mm
Diameter of housing	39 mm
Collet chuck diameter	6 mm
Suitable for max. sanding block diameter	16 mm
Max. HM rotating milling cutter diameter	10 mm
Weight	0.5 kg

EAN-Code

4251757301063