

Miniature cutting insert, type AW HW56 15

for chamfering and profile turning

ATORN[®]



Application

For chamfering and profile turning in the material groups of steel and (stainless steel) with low to high cutting speeds and medium cutting conditions.

Version

- solid carbide cutting insert, 45° chamfer angle with inner cooling

Advantage

- very hard cemented carbide type ensures low wear
- user-friendly chamfering and profile turning and precise chamfers with excellent finish quality
- extremely sharp cutting edges ensure cutting with process reliability

| | |
|---------------------------------|------------------------------------|
| Art. No. | 17128 170 |
| Shaft diameter | 6 mm |
| ISO name | AW |
| Length | 51 mm |
| Clearance length | 15 mm |
| Radius | 0.2 mm |
| Chamfer angle | 45 Degree |
| Bevel angle | 45 Degree |
| Programming size | 2.3 mm |
| Min. bore diameter | 1 mm |
| Holder size | 6 |
| Machining direction | Left |
| Carbide type | HW56 15 |
| Material to be processed | Stainless steel, Non-ferrous metal |

EAN-Code

4050293661293