



Figure similar

CIRCUIT BREAKER 3VA1 IEC FRAME 160 BREAKING  
CAPACITY CLASS S ICU=36KA @ 415 V 4-POLE,  
LINE PROTECTION TM210, FTFM, IN=80A  
OVERLOAD PROTECTION IR=80A FIXED SHORT  
CIRCUIT PROTECTION II=10 X IN NEUTRAL  
UNPROTECTED BUSBAR CONNECTION

Model		
product brand name		SENTRON
Product designation		Molded case circuit breaker
Design of the product		Line protection
Product variations		General Applications
Ground fault monitoring version		Without
Design of the auxiliary release		Without auxiliary release
Design of the auxiliary switch		Without
Design of the operating mechanism		toggle handle
Type of the driving mechanism / motor drive		No
Design of the overcurrent release		TM210
General technical data		
Number of poles		4
Trip class / of the L-trip / with I <sup>2</sup> t characteristic / initial value		1
Trip class / of the L-trip / with I <sup>2</sup> t characteristic / Full-scale value		1
Electrical endurance (switching cycles)		
• at AC-1 / at 380/415 V / at 50/60 Hz		8 000
circuit-breaker / Design		3VA
Mechanical service life (switching cycles) / typical		15 000
Voltage		
Insulation voltage / Rated value	V	800
Protection class		

Protection class IP		IP40
Protection class IP / on the front		IP40
Protective function of the overcurrent release		LI

#### Switching capacity

Switching capacity class of the circuit breaker		S
---	--	---

#### Dissipation

Active power loss		
• maximum	W	19.2

#### Electricity

Continuous current / Rated value / maximum	A	160
Continuous current / Rated value	A	80
Adjustable response value current		
• of the current-dependent overload release / Full-scale value	A	1
• of the instantaneous short-circuit release / initial value	A	10

#### Main circuit

Operating voltage		
• with AC / at 50/60 Hz / Rated value	V	690
• for DC / Rated value	V	600
Operating current		
• at 40 °C / Rated value	A	80
• at 50 °C / Rated value	A	80
• at 55 °C / Rated value	A	78
• at 60 °C / Rated value	A	77
• at 65 °C / Rated value	A	75
• at 70 °C / Rated value	A	74

#### Auxiliary circuit

Number of CO contacts / for auxiliary contacts		0
--	--	---

#### Suitability

Suitability for use		system protection
---------------------	--	-------------------

#### Adjustable parameters

Adjustable response value current		
• of I-trip / Full-scale value	A	10
• for N-conductor protection / initial value	A	0
• for N-conductor protection / Full-scale value	A	0
Adjustable response value current / of the current-dependent overload release / initial value	A	1

#### Product details

Product component		
-------------------	--	--

• Trip indicator		No
• display		No
• Voltage trigger		No
• undervoltage release		No
• undervoltage release with leading contact		No
<b>Product property</b>		
• for neutral conductors / upgradeable/retrofitable / Short-circuit and overload proof		No
Product expansion / optional / motor drive		Yes

#### Product function

<b>Product function</b>		
• Intrinsic device protection		Yes
• communication function		No
• Phase failure detection		No
• other measurement function		No

#### Accessories

Manufacturer article number / of the supplied basic switch		<a href="#">3VA1180-4ED42-0AA0</a>
--	--	------------------------------------

#### Short circuit

<b>Operational short-circuit current breaking capacity (Ics)</b>		
• at 240 V / Rated value	kA	55
• at 415 V / Rated value	kA	36
• at 440 V / Rated value	kA	25
• at 500 V / Rated value	kA	15
• at 690 V / Rated value	kA	5
<b>Maximum short-circuit current breaking capacity (Icu)</b>		
• at 240 V / Rated value	kA	55
• at 415 V / Rated value	kA	36
• at 440 V / Rated value	kA	25
• at 500 V / Rated value	kA	16
• at 690 V / Rated value	kA	7
<b>Short-circuit current making capacity (Icm)</b>		
• at 240 V / Rated value	kA	121
• at 415 V / Rated value	kA	75.6
• at 690 V / Rated value	kA	7.5

#### Connections

Arrangement of electrical connectors / for main current circuit		Front terminal
Type of connectable conductor cross-section		

- for flat-bar terminal connection / minimum
- for flat-bar terminal connection / maximum

12 x 0  
17 x 6.5

Type of electrical connection / for main current circuit

Lug terminal

## Mechanical Design

Height	mm	130
Width	mm	101.6
Depth	mm	70
Mounting type		fixed mounting

## Environmental conditions

### Ambient temperature

- during operation / minimum
- during operation / maximum
- during storage / minimum
- during storage / maximum

°C -25  
°C 70  
°C -40  
°C 80

## Certificates

### Equipment marking

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

Q  
Q

General Product Approval

EMC

Declaration of  
Conformity

Shipping Approval



[other](#)



other

[other](#)

## Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/3VA11804ED420AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3VA11804ED420AA0/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3VA11804ED420AA0](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA11804ED420AA0)

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



**last modified:**

11.03.2015