


PHYSICAL DIMENSIONS:

DA1206B102R-10

UNCONTROLLED DOCUMENT


A	3.20 [.126]	+ 0.20 [.008]
B	1.60 [.063]	+ 0.20 [.008]
C	0.80 [.031]	+ 0.20 [.008]
D	0.40 [.016]	+ 0.15 [.006]
D1	0.30 [.012]	+ 0.20 [.008]
E	0.80 [.031]	+ 0.10 [.004]




ELECTRICAL CHARACTERISTICS:

Z @ 100MHz (Ω)	DCR (Ω)	Rated Current
Nominal	1000	
Minimum	750	
Maximum	1250	0.8
LINE TO LINE INSULATION RESISTANCE >100 MΩ AT 75 VOLTS.		

- NOTES: UNLESS OTHERWISE SPECIFIED
1. TAPED AND REELED per CURRENT EIA SPECIFICATIONS 7" REELS, 3000 PCS/REEL.
 2. TERMINATION FINISH IS 100% TIN.
 3. COMPONENTS SHOULD BE ADEQUATELY PREHEATED BEFORE SOLDERING.





LAND PATTERNS FOR REFLOW SOLDERING



(For wave soldering, add 0.762 (0.030) to this dimension)

RECOMMENDED SOLDERING CONDITIONS



DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
E	CHANGE C DIMENSION	07/29/10	JUN	PROJECT/PART NUMBER: DA1206B102R-10	REV	PART TYPE:	DRAWN BY:
D	UPDATE COMPANY LOGO	05/19/09	JRK		E	CO-FIRE	TMB
C	D1 dim chgd from 0.008 ±0.004 to 0.012 ± 0.008. UPDATE COMPANY LOGO	10/30/07	JRK		DATE:	SCALE:	SHEET:
B	CHANGE C DIMS FROM .80 ADD RoHS	09/08/05	JRK		03/29/04	NTS	
A	ORIGINAL DRAFT	03/29/04	TMB	CAD #	TOOL #		
REV	DESCRIPTION	DATE	INT	DA1206B102R-10-E	-		2 of 2