

## CNC precision short drill chuck

In accordance with ISO 7388-1 (DIN 69871)

**ALBRECHT**  
Präzisionsspannhalter

### Application:

For use on machining centres and CNC machines with tool change systems. For drilling, reaming, countersinking and also light milling and finishing tasks.

### Execution:

- 100 % concentricity check using different test pin diameters at various measuring points, based on DIN ISO 10888.
- Concentricity tolerance  $\leq 0.03$  mm across the entire clamping range.
- With worm gear.
- Relevant parts hardened and ground.

### Advantage:

- Accident-proof as opening of the chuck during operation or on a sudden spindle stop is not possible.
- Integrated worm gear ensures high retention torque  $< 75$  Nm with 13 mm diameter.

### Delivery:

1x CNC precision short drill chuck in accordance with ISO 7388-1 (DIN 69871); incl. hexagon key.



<b>Art. no.</b>	<b>23050 540</b>
<b>Brand</b>	ALBRECHT
<b>Manufacturer Part Number</b>	800 110Z 240 0
<b>Tool holding device</b>	SK 40
<b>Min./max. clamping width</b>	0.5-10 mm
<b>Projecting length</b>	69 mm
<b>Outer diameter</b>	45 mm
<b>Length closed</b>	78 mm
<b>Tapered diameter</b>	38 mm
<b>Clear length</b>	37.5 mm
<b>Concentricity tolerance</b>	0.03 mm
<b>Coolant supply</b>	Internal axial
<b>Balancing quality</b>	G 2.5 at 20 rpm
<b>Gross Weight</b>	1.260 kg
<b>Product Group</b>	209

### EAN

4250261589332