


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0015247040](#)
Status: **Active**
Overview: Mini-Fit Family Power Connectors
Description: Mini-Fit BMI Receptacle Header, 4.20mm Pitch, Dual Row, Vertical, with Snap-In Plastic Pegs, Post 2.54µm Tin (Sn), UL 94V-2, 4 Circuits

Documents:

3D Model (PDF)	Packaging Specification PK-42385-999-001 (PDF)
Drawing (PDF)	Test Summary TS-5556-002-001 (PDF)
3D Model	RoHS Certificate of Compliance (PDF)
Product Specification PS-5556-002-001 (PDF)	



Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Receptacles
Series	42385
Application	Board-to-Board, Power, Wire-to-Board
Comments	Solder Type With Pegs, Solder Type With Pegs
Overview	Mini-Fit Family Power Connectors
Product Name	Mini-Fit BMI
UPC	800753640566

Physical

Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Natural
Durability (mating cycles max)	30
Flammability	94V-2
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Resin	Nylon
Net Weight	0.869/g
Number of Rows	2
Orientation	Vertical
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.00mm
Packaging Type	Tray
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	9.0A
Grounding to PCB	No
Voltage - Maximum	600V AC (RMS)/DC

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[42385](#) Series

Mates With

Panel Mount Plug [42475](#)
Right Angle
Headers [42404](#) , [43810](#)
Vertical
Headers [42440](#) , [43879](#) , [44068](#)

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-free Process Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	240

Material Info

Engineering Number	A-42385-04A1
--------------------	--------------

Reference - Drawing Numbers

Packaging Specification	PK-42385-999-001
Product Specification	PS-5556-002-001
Sales Drawing	SDA-42385-X-001
Symbol/Footprint Data	SYM-A42385-04XX
Test Summary	TS-5556-002-001

This document was generated on 01/19/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION