

1473562-3 ✓ ACTIVE

RITS | RITS Plug Connector


TE Internal #: 1473562-3

RITS Plug Connector, Standard Rectangular Connectors, Connector Assembly, Plug, Mating Alignment, Polarization Mating Alignment Type, Mating Retention

[View on TE.com >](#)



Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Connector Assembly**

Connector & Housing Type: **Plug**

Mating Alignment: **With**

Mating Alignment Type: **Polarization**

Mating Retention: **With**

### Features

#### Product Type Features

Glow Wire Rating	Standard Part - Not Glow Wire
Connector Type	Connector Assembly
Connector Product Type	Connector Assembly
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

#### Configuration Features

Preloaded	Yes
Number of Positions	3
Number of Rows	1

#### Electrical Characteristics

Operating Voltage	32 VDC
-------------------	--------

#### Contact Features



Contact Layout	Inline
Contact Type	Tab
Multiple Contact Types	Without
Shunts/Shorting Bars	Without
Wire Contact Termination Area Plating Material	Nickel
Contact Underplating Material	Nickel
Contact Mating Area Plating Material	Gold
Contact Retention Within Housing	Without
Contact Current Rating (Max)	3 A

#### Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

#### Mechanical Attachment

Panel Mount	No
PCB Mount Alignment	Without
Mating Alignment	With
Mating Alignment Type	Polarization
Mating Retention	With
Mating Retention Type	Latch
PCB Mount Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

#### Housing Features

Housing Color	Yellow
Housing Material	Thermoplastic GF
	.079 in

#### Dimensions

Width	5.05 mm[.198 in]
Height	18.5 mm[.728 in]
Length	14.1 mm[.555 in]

#### Usage Conditions

Operating Temperature Range	-30 – 75 °C[-22 – 167 °F]
-----------------------------	---------------------------

#### Operation/Application

Assembly Integration Feature	Without
------------------------------	---------



For Use With	Header
Halogen Free	Yes
Shielded	No
Circuit Application	Signal

### Identification Marking

Circuit Identification Feature	Without
--------------------------------	---------

### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

### Packaging Features

Packaging Quantity	36
Packaging Method	Tube

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




## Compatible Parts



TE Part # 1729940-1  
RITS HAND TOOL

## Also in the Series | RITS Plug Connector



Standard Rectangular Connectors(32)

## Customers Also Bought



TE Part #1-1903128-4  
DYNAMIC 1100 REC AND TAB HSG



TE Part #1473562-6  
RITS CONN. PLUG ASSY 6P YELLOW



TE Part #1-1747500-2  
DYNAMIC 4000 REC AND TAB CONT



TE Part #1-1473562-6  
RITS CONN. PLUG ASSY 6P RED



TE Part #1473562-4  
RITS CONN. PLUG ASSY 4P YELLOW



TE Part #1-1746741-3  
RITS CONN. SOCKET ASSY 3P RED



TE Part #914594-1  
WIRE DEPRESSOR



TE Part #1-692930-4  
DEPRESSOR, SHEAR

## Documents

### Product Drawings

[RITS CONN. PLUG ASSY 3P YELLOW](#)

English

### CAD Files



### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1473562-3\\_F.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1473562-3\\_F.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1473562-3\\_F.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[Remote Input Output Terminal System \(RITS\) Connectors](#)

English

### Product Specifications

[Product Specification](#)

Japanese

### Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English

### Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

Japanese

[RITS Connector Interconnection System/e-CON Connector](#)

Japanese

[Instruction Sheet \(non U.S.\)](#)

Japanese

[HAND TOOL FOR RITS PLUG SOCKET ASSEMBLY](#)

Japanese