

91569-1 ✓ ACTIVE

AMP

TE Internal #: 91569-1

Portable Crimp Tools, Premium Crimp Tooling, Not Releasable,
Not Adjustable, Fixed In Tool, TE Product Specification (114-)

[View on TE.com >](#)



Application Tooling > Portable Crimp Tools



Tool Grade: **Premium Crimp Tooling**

Ratchet Configuration: **Not Releasable, Not Adjustable**

Die Sets Type: **Fixed In Tool**

Specification Type: **TE Product Specification (114-)**

Certification: **Yes – Certificate Included**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Premium Crimp Tooling
Ratchet Configuration	Not Releasable, Not Adjustable
Die Sets Type	Fixed In Tool
Specification Type	TE Product Specification (114-)
Certification	Yes – Certificate Included
Power Type	Battery, Electric, Manual
Tool Type	CERTI-CRIMP II, Straight Action Hand Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2020 (205) Candidate List Declared Against: JUN 2016 (169) Does not contain REACH SVHC
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2020 (205)



Candidate List Declared Against: JUN 2016 (169)

Halogen Content Not Yet Reviewed for halogen content

Solder Process Capability Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.


Compatible Parts



TE Model / Part # CAT-P87024-R2435
Power Double Lock Receptacle



TE Model / Part # CAT-P87024-T111
Power Double Lock Tab




TE Model / Part # 179593-1
AMP POWER D/LOCK RECCONT. L/P




TE Model / Part # 179593-2
POWER D/LOCK REC CONT. H/P L/P




TE Model / Part # 177915-9
POWER DBL LOCK REC CONT



TE Model / Part # 1-177917-2
AMP POWER DBL LOCK TAB(L)



TE Model / Part # 177917-2
AMP POWER DBL BLOCK TAB(L)



TE Model / Part # 179595-2
AMP POWER D/LOCK TAB CONT, L/P

Customers Also Bought




TE Model / Part #177907-1
POWER DBL LOCK CAP P/M 3P



TE Model / Part #234914-1
EXT TOOL FOR POWER DBL LOK TAB




TE Model / Part #91567-1
CERTICRIMP 2 26-22 POWER DL



TE Model / Part #234912-1
EXT TOOL FOR POWER DBL LOK REC



TE Model / Part #917242-8
DYNAMIC D-3500 WTW TAB HSG 20P



TE Model / Part #179593-1
AMP POWER D/LOCK RECCONT. L/P



TE Model / Part #179593-2
POWER D/LOCK REC CONT. H/P L/P

Documents

Datasheets & Catalog Pages

[CERTI-CRIMP II-Premium-August-1-1773864-7](#)

English

[CERTI-CRIMP II TOOL DATA SHEET .040, CT, EP, POWER DBL LOCK & DRAWER CONTACTS](#)

English

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English

[Crimp Term Whitepaper-Use the Right Tool 1-1773953-1](#)

English

Bottoming Dies

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English