

## SDNC clamp holder, positive, neutral

For longitudinal turning with DC indexable insert

**ATORN**<sup>®</sup>

### Application


For longitudinal turning with DC indexable insert, 55°

### Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 62.5°, tip angle 90°, clearance angle 7°
- SDNCN 12 12 F07

### Advantage

- very slim geometry, optimised for contour turning work
- Positive geometry for the body ensures low cutting forces
- Very good surface quality for medium infeed and finishing



<b>Art. No.</b>	<b>17861 015</b>
<b>ISO name</b>	SDNC N 1010 E07
<b>Shaft height</b>	10 mm
<b>Shank width</b>	10 mm
<b>Length</b>	70 mm
<b>Length of head</b>	16 mm
<b>Programming size</b>	5 mm
<b>Suitable for indexable inserts</b>	DC.. 0702..
<b>Tool design</b>	Neutral
<b>DIN</b>	4983

### EAN-Code

4050293348507