

Collet chuck extension

With internal cooling and straight shank

diebold

Application:

For clamping tools with a straight shank.

Execution:

- With straight shank, type ER standard.
- Particularly slim version for use in milling chucks as tool extension for deep machining operations where space is restricted.
- Wrench no. 23308 008 and collets 23320.
- Wrench no. 23308 008 and collets 23320.

Delivery:

1x collet chuck extension.



| | |
|---------------------------------|------------------|
| Art. no. | 23304 190 |
| Brand | DIEBOLD |
| Manufacturer Part Number | 74.010.190 |
| Collet type | ER 20 |
| Shank diameter | 20 mm |
| Min./max. clamping range | 1-13 mm |
| Width across flats | 30 mm |
| Outer diameter | 34 mm |
| Shaft length | 60 mm |
| Length of head | 36 mm |
| Gross Weight | 0.233 kg |
| Product Group | 2AB |