## **Schottky Rectifier**

# multicomp PRO



### Features:

- · For surface mounted applications
- Metal-Semiconductor junction with guarding
- · Epitaxial construction
- Very low forward voltage drop
- High current capability
- Plastic material has UL flammability classification 94V-0
- For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications.

## Mechanical Data:

| Case            | : Molded Plastic              |
|-----------------|-------------------------------|
| Polarity        | : Colour band denotes cathode |
| Weight          | : 0.002 ounces,0.053 grams    |
| Reverse Voltage | : 20 to 150 Volts             |
| Forward Current | : 1 Ampere                    |

## Maximum Ratings and Electrical Characteristics:

Rating at 25°C ambient temperature unless otherwise specified. Single phase, half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.

| Characteristics   | Symbol | SS12+          | SS14+    | SS16+        | SS110+     | SS115+       | Unit |
|---|--------|----------------|----------|--------------|------------|--------------|------|
| Max. Repetitive Peak Reverse Voltage  | Vrrm   | 20             | 40       | 60           | 100        | 150          |      |
| Max. RMS Voltage  | VRMS   | 14             | 28       | 42           | 70         | 105          | V    |
| Max. DC Blocking Voltage  | VDC    | 20             | 40       | 60           | 100        | 150          |      |
| Max. Average ForwardRectified CurrentTL= 100°C  | I(AV)  | 1              |          |              |            |              |      |
| Peak Forward Surge Current,<br>8.3ms Single Half Sine-wave<br>Superimposed on Rated Load (JEDEC method) | IFSM   | 30             |          |              |            | A            |      |
| Max. Instantaneous Forward Voltage (Note 1)<br>F = 1A at 25°C<br>at 100°C                               | VF     | -              | .5<br>.4 | 0.75<br>0.65 | 0.8<br>0.7 | 0.95<br>0.85 | V    |
| Max. DC Reverse Current atTJ = 25°CRated DC Blocking Voltage atTJ = 125°C                               | lr     | 0.2 0.1<br>- 2 |          |              | μA         |              |      |
| Typical Junction Capacitance (Note 2)   | CJ     | 110            |          |              | рF         |              |      |
| Typical Thermal Resistance (Note 3)   | Rejl   | 28             |          |              | °C/W       |              |      |
| Operating Temperature Range   | TJ     | -65 to +150    |          |              | °C         |              |      |
| Storage Temperature Range   | Tstg   |                |          |              |            |              |      |

#### Notes:

1. Pulse test with PW=300µs, 1% duty cycle

2. Measured at 1MHz and applied reverse voltage of 4V DC.

3. Thermal resistance junction to lead.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



## **Ratings and Characteristic Curves**







FIG. 3 TYPICAL FORWARD CHARACTERISTICS











FIG. 6 TYPICAL TRANSIENT THERMAL IMPEDANCE




Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

# multicomp PRO

## **Schottky Rectifier**

**Dimensions:** 



Dimensions : Inches (Millimetres)

### **Part Number Table**

| Description                                  | Part Number |  |  |
|--|-------------|--|--|
| Surface Mount<br>Schottky Barrier Rectifiers | SS12+       |  |  |
|  | SS14+       |  |  |
|  | SS16+       |  |  |
|  | SS110+      |  |  |
|  | SS115+      |  |  |

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

