


E20615



Fibre optic through beam sensor

FE-11-EPA-M4/F16X0,265/2M



Application

Function principle Through-beam sensor

Detection zone

Range with fibre optic amplifier type OB50; OBF; OO50

OB50

Range of fibre optics [mm] 150

OBF

Range of fibre optics [mm] 210

OO50

Range of fibre optics [mm] 800

Operating conditions

Ambient temperature [°C] -40...70

E20615



Fibre optic through beam sensor

FE-11-EPA-M4/F16X0,265/2M

Mechanical data	
Weight [g]	47
Version of sensing head	straight
Sensing head thread	M4
Sensing head length [mm]	15
Total length [mm]	2000
Min. bending radius [mm]	9
Fibre arrangement	
Core diameter [mm]	16 x 0.25
Fibre material	PMMA
Fibre head material	aluminium
Fibre sheath material	PE
Accessories	
Accessories (supplied)	hexagon nuts: 4 x M4 tooth lock washers: 4
Accessories (optional)	Cutter for fibre optics, E20600
Remarks	
Pack quantity	1 pcs.