

Short-length chucks

ERICKSON system with straight shank

ORION[®]

Application:

For use on NC and CNC machining equipment.

Execution:

- Min. tensile strength at core 800 N/mm.
- Hardened.
- Clamping of drill bits on drill heel possible.
- With adjustable longitudinal stop.
- Collets no. 23326.

Advantage:

- With straight shank - extremely slim version.
- Very good accessibility in confined spaces.

Delivery:

1x ERICKSON short chuck system with cylindrical shank.



Art. no.	23325 320
Brand	ORION
Manufacturer Part Number	23325320
Collet type	DK 10
Shank diameter	25 mm
Min./max. clamping width	2.5-14.5 mm
Width across flats	24 mm
Outer diameter	27 mm
Shaft length	76 mm
Length of head	49 mm
Min. clamp in depth	55 mm
Max. clamp in depth	107 mm
Gross Weight	0.310 kg
Product Group	218

EAN

4039247157013