



HCS CARBON STEEL BLADES FOR WOOD




FEATURES

- HCS jigsaw blades offer high durability and best cutting results
- Consisting of flexible carbon steel (HCS)
- For use in wood, plastic-coated wood fibre boards and plastics.



FOR USE WITH

Jigsaws (corded and cordless).



PACKS

Cat. No.	Application	Total length mm	Working length mm	Teeth pitch mm	Max. cutting depth mm	Bosch Cat. No.	Pack Qty.
DT2050-QZ	Especially for curved cuts in softwood, plywood, plywood and fiber boards.	76	48	2	15	T119B0	5
DT2052-QZ	Especially for curved cuts in softwood, plywood, plywood and fiber boards.	116	87	3	65	T301CD	5
DT2053-QZ	By reverse gear splinter-free cuts in wood, chipboard, plywood, fibreboard and laminate (bevel).	100	73	2.5	40	T101BR	5
DT2164-QZ	Fast, straight cuts in wood, and wood materials.	100	68	4	60	T101D	5
DT2165-QZ	Straight, fine cuts in wood, wood materials and plastics.	100	73	2.5	30	T101B	5
DT2168-QZ	Fine curve cuts in softwood, plywood and coated boards.	76	47	1.4	30	T101A0	5
DT2049-QZ	Fast, extra straight cuts in wood and chipboard.	100	68	4	60	T101DP	5
DT2051-QZ	Fast, rough cuts in wood, chipboard, plywood and fiber boards.	132	100	4	85	T301DL	5
DT2077-QZ	Fast curve cuts in wood.	100	70	4	60	T244D	5
DT2166-QZ	Fast, straight cuts in wood, chipboard, carpentry and fiber boards.	100	68	4	60	T144D	5
DT2186-QZ	Fast, straight cuts in wood, chipboard, plywood, laminated chipboard and plastic up to 60mm thick.	100	68	4	60	T144D	100
DT2169-QZ	Fast, straight cuts in wood and wood materials.	152	116	4	100	T344D	5
DT2048-QZ	For straight and cuts at accurate angles in wood, chipboard, carpentry and fiber boards	116	87	2.5	65	T301BCP	5
DT2075-QZ	Fast, extra straight and angular cuts in wood, chipboard, carpentry and fiber boards.	100	68	4	60	T144DP	5
DT2076-QZ	Fast, extra straight and angular cuts in wood, chipboard, carpentry and fiber boards.	152	116	4	100	T344DP	5
DT2057-QZ	Quick cuts in varying thicknesses in wood, chipboard, joiner and fiber boards up to 65mm.	116	91	2-3	65	T234X	5
DT2167-QZ	Fast, rough cuts in thick wooden planks up to 120mm thickness.	180	155	4	120	T744D	5
DT2060-QZ	Straight, clean cuts in wood, chipboard, plywood, fiber boards and plastics, with U-shank	100	78	2.5	30	U101B	5
DT2061-QZ	Fast cuts in wood and chipboard, with U-shank.	100	76	4	60	U144D	5
DT2074-QZ	Clean, extra straight and angled cuts in wood, plywood, carpentry and fiber boards for border flush cuts	112	74	2.3	65		1

JIGSAW BLADES - QUICK REFERENCE CHART

		Wood Blades						
		High Carbon Steel						
DOC	Pitch	Laminates / Hardwood	Curved cuts in wood	Wood	Wood / Plywood / Laminates / Plastic	Aluminium / Plastics	Softwood / Plywood / Fibre Boards	Wood / Chipboard / Plywood / Laminate / Fibre Board
15mm	15mm				DT2205			
15mm	2.0mm				DT2216		DT2050	
30mm	1.4mm						DT2168	
30mm	2.5mm				DT2217, DT2165			DT2060 (U Shank)
30mm	3.0mm					DT2221		
40mm	2.5mm	DT2207, DT2219						DT2053
60mm	3.1mm				DT2211, DT2212			
60mm	4.0mm		DT2077	DT2164, DT2049, DT2061 (U Shank)	DT2218, DT2220			DT2166, DT2075
60mm	4.2mm				DT2209, DT2210, DT2213, DT2214, DT2186			
65mm	2mm & 3mm							DT2057
65mm	2.3mm							DT2074 (Flush cut)
65mm	2.5mm							DT2048
65mm	3.0mm						DT2052	
85mm	4.0mm							DT2051
100mm	4.0mm			DT2169				DT2076
120mm	4.0mm			DT2167				

		Metal Blades			
		Bi-Metal	HSS		
DOC	Pitch	Steel / Non-Ferrous	Steel / Non-Ferrous	Aluminium / Non Ferrous	Multi Material
2.0mm	0.7mm		DT2162		
3.0mm	1.2mm			DT2085	
3.0mm	1.0mm	DT2150			
2.5mm	0.8mm	DT2156			
4.0mm	1.54mm	DT2054			
6.0mm	1.8mm	DT2154			
4.0mm	1.2mm		DT2160		
6.0mm	2.0mm		DT2161		
30mm	3mm				Alu 15mm, Metal, 6mm, Plastic 30mm

		Specialist Blades						
		TCT	TCT	Bi-Metal	TC Grit	Knife Blade	Bi-Metal	Bi-Metal
DOC	Pitch	GRP / Plastic / Plaster	Inox	Laminates	Ceramic / Fibreglass	Soft Materials / Rubber / Foam / Polystyrene	Sandwich Materials / Steel	Wood / Metal
3.0mm	1.0mm		DT2101					
5.0mm	1.4mm		DT2055					
10mm	n/a							
15mm	1.4mm			DT2081				
15mm	1.7mm			DT2080				
20mm	4.3mm	DT2103						
65/10mm	2.4-5mm							DT2059 (Wood 65mm / Metal 10mm)
65mm	4.3mm	DT2056						
100mm	n/a					DT2201		
120mm	2.0mm						DT2084	