


90° DKJ - Pressarmatur Typ XPKU ../9 / 90° DKJ fitting type XPKU ../9
JIC Dichtkopf (74°Innenkonus) mit UNF-Überwurfmutter
JIC sealing cone (74° inside cone) with UNF union nut

Art. Nr. Art. N°	Bezeichnung Description	Standard	DN	G1	S1
224.001	XPKU 06 7/16" /9	•	06	7/16"	15
224.002	XPKU 06 1/2" /9		06	1/2"	17
224.003	XPKU 06 9/16" /9		06	9/16"	19
224.004	XPKU 08 1/2" /9	•	08	1/2"	17
224.005	XPKU 08 9/16" /9		08	9/16"	19
224.023	XPKU 08 3/4" /9		08	3/4"	24
224.006	XPKU 10 1/2" /9		10	1/2"	17
224.007	XPKU 10 9/16" /9	•	10	9/16"	19
224.008	XPKU 10 3/4" /9		10	3/4"	24
224.009	XPKU 12 3/4" /9	•	12	3/4"	24
224.010	XPKU 12 7/8" /9		12	7/8"	27
224.011	XPKU 12 1.1/16" /9		12	1.1/16"	32
224.012	XPKU 16 7/8" /9	•	16	7/8"	27
224.013	XPKU 16 1.1/16" /9		16	1.1/16"	32
224.015	XPKU 20 1.1/16" /9	•	20	1.1/16"	32
224.016	XPKU 20 1.3/16" /9		20	1.3/16"	36
224.017	XPKU 20 1.5/16" /9		20	1.5/16"	38
224.024	XPKU 25 1.1/16" /9		25	1.1/16"	32
224.019	XPKU 25 1.5/16" /9	•	25	1.5/16"	38
224.025	XPKU 25 1.5/8" /9		25	1.5/8"	50
224.020	XPKU 32 1.5/8" /9	•	32	1.5/8"	50

90° DKJ - Pressarmatur Kompaktbauweise Seite 36
90° DKJ fitting compact version on page 36



AGJ - Pressarmatur Typ XPAU / AGJ fitting type XPAU
JIC Außengewinde (74°Außenkonus)
JIC male thread (74° outside cone)

Art. Nr. Art. N°	Bezeichnung Description	Standard	DN	G1	S1
225.001	XPAU 06 7/16"	•	06	7/16"	12
225.002	XPAU 06 1/2"		06	1/2"	14
225.003	XPAU 06 9/16"		06	9/16"	15
225.020	XPAU 08 1/2"	•	08	1/2"	14
225.018	XPAU 08 9/16"		08	9/16"	15
225.019	XPAU 08 3/4"		08	3/4"	19
225.004	XPAU 10 1/2"		10	1/2"	14
225.005	XPAU 10 9/16"	•	10	9/16"	15
225.006	XPAU 10 3/4"		10	3/4"	19
225.021	XPAU 10 7/8"		10	7/8"	24
225.007	XPAU 12 3/4"	•	12	3/4"	19
225.008	XPAU 12 7/8"		12	7/8"	24
225.009	XPAU 12 1.1/16"		12	1.1/16"	27
225.010	XPAU 16 7/8"	•	16	7/8"	24
225.011	XPAU 16 1.1/16"		16	1.1/16"	27
225.012	XPAU 20 1.1/16"	•	20	1.1/16"	27
225.013	XPAU 20 1.3/16"		20	1.3/16"	32
225.014	XPAU 20 1.5/16"		20	1.5/16"	34
225.022	XPAU 25 1.1/16"		25	1.1/16"	27
225.015	XPAU 25 1.5/16"	•	25	1.5/16"	34
225.023	XPAU 25 1.5/8"		25	1.5/8"	42
225.016	XPAU 32 1.5/8"	•	32	1.5/8"	42
225.024	XPAU 32 1.7/8"		32	1.7/8"	50
225.017	XPAU 40 1.7/8"	•	40	1.7/8"	50



Standard Standardgröße / Standard size
DN Durchmesser Nominal / Diameter nominal
G1 Gewinde / Thread
S1 Schlüsselweite / Hexagon