

DSM Series Ultra Thin Surface Mount Single Digit 7-Segment LED Display

DSM7UA70105 - 0.70" (17.78mm) Digit Height Emitting Color: Pure Green (InGaN/GaN)

Applications

- People Movers
- Home Appliances
- Medical Devices
- Industrial Devices
- Automation and Controls
- Light Control


- IoT
- Transportation
- Food Service Appliances

Key Features


- 1-digit seven segment led numeric display
- Outer dimensions: 24.0 x 14.8 x 2.3mm
- Reduce overall thickness of PCB, with major cost savings
- Available in 4 different digit heights and widths
- Excellent character appearance, with high light output
- Super green chip
- Made from InGaN on transparent GaN substrate
- Made of white segments and gray surface
- Also available in super bright red
- Available in cut tape or automation-friendly tape and reel

- Exclusive patented technology
- Low current operation and lower power consumption
- Polarity: common anode
- Available for reverse mounting configuration
- Side by side mounting allows space saving
- Easy mounting on PC boards or sockets
- Moisture Sensitive Level (MSL): 2a
- Life expectancy: 100,000 hours
- Technically and mechanically rugged
- Quality tested with the highest industry standard


Ordering Data



Dimensions and Internal Circuit Diagram




Dimensions in millimeters [inches] Tolerance is ±0.25mm [.01"] unless otherwise noted



Dimensions in millimeters [inches] Tolerance is ± 0.25 mm [.01"] unless otherwise noted

Pin Connections (Common Anode)



| PIN No | Connection | | |
|--------|--------------|--|--|
| 1 | CATHODE E | | |
| 2 | CATHODE D | | |
| 3 | COMMON ANODE | | |
| 4 | CATHODE C | | |
| 5 | CATHODE DP | | |
| 6 | CATHODE B | | |
| 7 | CATHODE A | | |
| 8 | COMMON ANODE | | |
| 9 | CATHODE F | | |
| 10 | CATHODE G | | |

Product Specifications

| Absolute Maximum | Rating at | Ta=25°C / | 77°F (Ta= | Ambient ⁻ | Temperature) |
|------------------|-----------|-----------|-----------|----------------------|--------------|
| | | | | | |


| Parameter | Symbol | Maximum Rating | Unit |
|--------------------------------------|------------------|----------------------------|------------|
| Power dissipation | P _{AD} | 120 | mW |
| Derating liner from 25°C/77°F | - 0.30/9.46 | | mA °C / °F |
| Continuous forward current | I _{AF} | 30 | mA |
| Peak current (duty cycle 1/10, 1kHz) | I _{PF} | 100 | mA |
| Reverse voltage | V _R | 5 | V |
| Operating temperature | T _{OPR} | -40 TO +105 -40 TO +221 | °C °F |
| Storage temperature | T _{STG} | -40 TO +105 -40 TO +221 | °C °F |

Electrical - Optical Characteristics at Ta=25°C / 77°F (Ta= Ambient Temperature)

| Charateristic | Symbol | Condition | Min. | Тур. | Max. | Unit |
|------------------------------|----------------|----------------------|------|------|------|------|
| Forward Voltage, (Per Dice) | V _F | I _F =20mA | - | 2.8 | 3.6 | V |
| Reverse Current, (Per Dice) | I _R | V _R =8V | - | - | 10 | μA |
| Dominant Wavelength | λ_D | I _F =20mA | 515 | - | 530 | nm |
| Luminous Intensity | I _v | I _F =20mA | 350 | - | 700 | mcd |
| Spectral radiation bandwidth | Δλ | I _F =20mA | - | 30 | - | nm |


4

Product Specifications




Circuit Design Notes

- · Always use current limit resistors when necessary
- LEDs could be electrically connected in parallel, with each LED having its own current limiting resistor



• SMT Reflow Soldering Instructions



- We recommend the reflow temperature 245°C / 473°F (+/- 5°C / 41°F). The maximum soldering temperature should be limited to 260°C / 500°F .
- Number of reflow process shall be 2 time or less.
- Soldering Iron

Basic spec is ≦4 sec when 260°C / 500°F. If temperature is higher, time should be shorter (+10°C / 50°F →1 sec). Power dissipation of Iron should be smaller than 15W, and temperature should be controllable. Surface temperature of the device should be under 230°C /446°F.

- Rework
 - Customer must finish rework within 3 sec. under 350°C / 662°F.
 - The head of soldering iron cannot touch copper foil.

Storage Condition


In factory original sealed bag package


| TEMPERATURE CONDITION | HUMIDITY CONDITION |
|-----------------------|--------------------|
| 5°C ~ 30°C | Below 60%RH |

After opened and not in factory original sealed bag package

| | · · · · · · · · · · · · · · · · · · · | |
|-----------------------|---------------------------------------|----------------------------------|
| TEMPERATURE CONDITION | HUMIDITY CONDITION | STORAGE TIME |
| 5°C ~ 30°C | Below 60%RH | Within 4 weeks (MSL as level 2a) |

Tape & Reel Dimensions





Dimensions in millimeters

Compliance and Approvals

