

## RANA LED Surface 1200

RANA LED S 1200 HO 3K LOUV+PRI 1-10 W GEN2

0051489



### Product features

- Surface or Suspended LED Linear luminaire with Louvre + Prismatic Optic, Direct Light Distribution, Luminaire Dimensions: 1160x187x47mm, Sylvania White body colour, IP20, IK07, Light Engine Dimensions: 1130x165mm, 1-10V Dimmable, Low LED flicker (+/-5%), Warm White (3000K) LED Colour Temperature, 5800lm, 52W, 112lm/W efficacy, CRI>80, 3 SDCM (3-step MacAdam ellipse) LED Colour Consistency, UGR<19, Luminance at 65° < 3000 cd/m2, Lumen Maintenance: L90B10 at 50,000 hours, Quick electrical connection with push-connectors in the luminaire, Glow Wire Test 850°C.



### PRODUCT OVERVIEW

Product name	RANA LED S 1200 HO 3K LOUV+PRI 1-10 W GEN2
Technology	LED
Cap/Base	N/A
Housing	Steel
Mount	Ceiling surface mounting, Suspended
General application	Office, Hospitality, Retail, Education
ETIM Class	EC002892
E-number FI	4273662
Warranty	5 years
Fixture luminous flux (lm)	5800
Luminous flux (lm)	5800
Luminaire efficacy (lm/W)	112
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Glare control	< 19
Photobiological Risk Group	RG0
Total power consumption (W)	52
Electrical protection	Class I
Control gear type	Other
Dimmable	Yes
Dimming method	1-10V (Analogue)
Minimum dimming level (%)	10
Housing colour	White
IP rating	IP20
IK rating	IK07
Product EAN number	5410288514895

### DATA TABLE

## RANA LED Surface 1200

*RANA LED S 1200 HO 3K LOUV+PRI 1-10 W GEN2*

0051489

### General data

Product name	RANA LED S 1200 HO 3K LOUV+PRI 1-10 W GEN2
Technology	LED
Cap/Base	N/A
Housing	Steel
Mount	Ceiling surface mounting, Suspended
General application	Office, Hospitality, Retail, Education
Performance ambient temperature Tq (°C)	25
ETIM Class	EC002892
E-number FI	4273662
Warranty	5 years

### Optical data

Fixture luminous flux (lm)	5800
Luminous flux (lm)	5800
Luminaire efficacy (lm/W)	112
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Glare control	< 19
Photobiological Risk Group	RG0

### Electrical data

Total power consumption (W)	52
Mains voltage (V)	220-240V
Lamp power factor	0.95
Electrical protection	Class I
Control gear required	No
Control gear type	Other
Dimmable	Yes
Dimming method	1-10V (Analogue)
Minimum dimming level (%)	10
Drive current (mA)	275
Inrush Current (A)	45
Inrush Duration (µs)	100
Glow Wire Test (°C)	850
Energy Efficiency Class (A->G) of contained light source	C
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	31
Max. Luminaires per 16A C Breaker	51
Max. Luminaires per 20A C Breaker	62
Max. Luminaires per 10A B Breaker	18
Max. Luminaires per 16A B Breaker	30
Max. Luminaires per 20A B Breaker	37

### Lifetime data

Lifespan L70 B50	50000
------------------	-------

## RANA LED Surface 1200

RANA LED S 1200 HO 3K LOUV+PRI 1-10 W GEN2

0051489

Lifespan L70 B10	50000
Lifespan L80 B50	50000
Lifespan L80 B10	50000
Lifespan L90 B50	50000
Lifespan L90 B10	50000



### Physical data

Housing colour	White
IP rating	IP20
IK rating	IK07
Diffuser finish	Prismatic
Diffuser material	PC Polycarbonate
Nominal Product Length (mm)	1160
Nominal Product Width (mm)	187
Nominal Product Height (mm)	47
Weight (kg)	3.3

### Packaging

Single packaging type	Carton
Product EAN number	5410288514895
Packaging single length / height (cm)	153.5
Packaging single width (cm)	6.5
Packaging single depth (cm)	21.0
DUN14 (outer)	05410288514895
Units per outer package	1
Packaging outer length / height (cm)	153.5
Packaging outer width (cm)	6.5
Packaging outer depth (cm)	21.0

## PHOTOMETRY



## TECHNICAL DRAWINGS

## RANA LED Surface 1200

*RANA LED S 1200 HO 3K LOUV+PRI 1-10 W GEN2*

0051489

