

Load cells SAUTER CP P4 · CP P1 · CP P3



#### CP P4 · CP Y4

Single-point load cells made of anodised aluminium

STANDARD







- · CP P4: Accuracy in accordance with OIML R60 C3
- CP Y4: Accuracy in accordance with OIML R60 C2
- · CE and RoHS compliant
- Dust and spray protection to IP65 (in accordance with EN 60529)
- · Aluminium, anodised
- · Suitable for price-computing scales, bench scales, platform scales, etc.
- · Maximum platform size 200×200 mm
- 4-wire connection

Model

• Nominal sensitivity: 0,9 mV/V

Nominai ioad	
kg	
0,3	
0,6	
Nominal load	
kg	
0,3	
0,3 1,5	
<u>_</u>	
1,5	
	0,3 0,6

Nominal load

#### CP P1 · CP Y1

Single-point load cells made of anodised aluminium

STANI	DARD	)	
<b>∆ ∆</b> IP 6	<u> </u>	M	1 DAY
CB B1			

- · CP P1: Accuracy in accordance with OIML R60 C3
- CP Y1: Accuracy in accordance with OIML R60 C2
- · CE and RoHS compliant
- · Dust and spray protection to IP65 (in accordance with EN 60529)
- Aluminium, anodised
- · Suitable for price-computing scales, bench scales, platform scales, etc.
- Maximum platform size 250×350 mm
- 4-wire connection

Model

CP 35-3P1

CP 40-3P1

CP 50-3P1

- · Nominal sensitivity: 2 mV/V
- Note: Version in accordance with OIML R60 C4 or C5 on request

SAUTER	kg	
CP 3-3P1	3	
CP 5-3P1	5	
CP 6-3P1	6	
CP 8-3P1	8	
CP 10-3P1	10	
CP 15-3P1	15	
CP 20-3P1	20	
CD 30_3D1	30	

Nominal load

35

40

50

Model Nominal load

SAUTER	kg	
ECO design (without EC type approval)		
CP 3-2Y1	3	
CP 5-2Y1	5	
CP 10-2Y1	10	
CP 15-2Y1	15	
CP 20-2Y1	20	
CP 30-2Y1	30	

#### CP P3

Single-point load cells made of anodised aluminium

STANDARD		OPTION	
444		DAkkS	
IP 65	1 DAY	+3 DAYS -	

- · Accuracy in accordance with OIML R60 C3
- · CE and RoHS compliant
- Dust and spray protection to IP65 (in accordance with EN 60529)
- · Suitable for price-computing scales, bench scales, platform scales, etc.
- Maximum platform size 350×400 mm
- · 4-wire connection
- · Nominal sensitivity: 2 mV/V
- · Note: Version in accordance with OIML R60 C4 on request

Model	Nominal load	
SAUTER	kg	
CP 30-3P3	30	
CP 40-3P3	40	
CP 50-3P3	50	
CP 75-3P3	75	
CP 100-3P3	100	

## **MEASURING TECHNOLOGY & TEST SERVICE 2023**

SAUTER PICTOGRAMS





#### Adjusting program (CAL):

For quick setting of the instrument's accuracy. External adjusting weight required



#### Calibration block:

Standard for adjusting or correcting the measuring device



#### Peak hold function:

Capturing a peak value within a measuring process



#### Scan mode:

Continuous capture and display of measurements



#### Push and Pull:

The measuring device can capture tension and compression forces



#### Length measurement:

Captures the geometric dimensions of a test object or the movement during a test process



#### Focus function:

Increases the measuring accuracy of a device within a defined measuring range



#### Internal memory:

To save measurements in the device memory



#### Data interface RS-232:

Bidirectional, for connection of printer and PC



#### Profibus:

For transmitting data, e.g. between scales, measuring cells, controllers and peripheral devices over long distances. Suitable for safe, fast, fault-tolerant data transmission. Less susceptible to magnetic interference.



#### **Profinet:**

Enables efficient data exchange between decentralised peripheral devices (balances, measuring cells, measuring instruments etc.) and a control unit (controller). Especially advantageous when exchanging complex measured values, device, diagnostic and process information. Savings potential through shorter commissioning times and device integration possible



## Data interface USB:

To connect the measuring instrument to a printer, PC or other peripheral devices



#### Bluetooth\* data interface:

To transfer data from the balance/ measuring instrument to a printer, PC or other peripherals



#### WLAN data interface:

To transfer data from the balance/ measuring instrument to a printer, PC or other peripherals



#### Data interface Infrared:

To transfer data from the measuring instrument to a printer, PC or other peripheral devices



### **Control outputs**

(optocoupler, digital I/O): To connect relays, signal lamps,

valves, etc.



### Analogue interface:

To connect a suitable peripheral device for analogue processing of the measurements



#### Analog output:

For output of an electrical signal depending on the load (e.g. voltage 0 V - 10 V or current 4 mA - 20 mA)



#### Statistics:

Using the saved values, the device calculates statistical data, such as average value, standard deviation etc.



#### PC Software:

To transfer the measurement data from the device to a PC



#### Printer:

A printer can be connected to the device to print out the measurement



#### Network interface:

For connecting the scale/measuring instrument to an Ethernet network



## **KERN Communication Protocol (KCP):**

It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems



## GLP/ISO record keeping:

Of measurement data with date, time and serial number. Only with SAUTER printers



## Measuring units:

Weighing units can be switched to e.g. non-metric. Please refer to website for more details



Measuring with tolerance range (limit-setting function):
Upper and lower limiting can be programmed individually. The process is supported by an audible or visual signal, see the relevant model



# Protection against dust and water splashes IPxx:

The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989+A1:1999+A2:2013

#### ZERO:

Resets the display to "0"



#### **Battery operation:**

Ready for battery operation. The battery type is specified for each device



#### Rechargeable battery pack:

Rechargeable set



#### Plug-in power supply:

230V/50Hz in standard version for EU. On request GB, AUS or USA version available



## Integrated power supply unit: Integrated, 230V/50Hz in EU.

More standards e.g. GB, AUS or USA on request



#### Motorised drive:

The mechanical movement is carried out by a electric motor



#### Motorised drive:

The mechanical movement is carried out by a synchronous motor (stepper)



#### Fast-Move:

The total length of travel can be covered by a single lever movement



#### Verification possible:

Models with type approval for construction of verifiable systems



#### DAkkS calibration possible:

The time required for DAkkS calibration is shown in days in the pictogram



#### Factory calibration:

The time required for factory calibration is specified in the pictogram



#### Package shipment:

The time required for internal shipping preparations is shown in days in the



#### Pallet shipment:

The time required for internal shipping preparations is shown in days in the pictogram

**<sup>→</sup>**0+

<sup>\*</sup>The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by KERN & SOHN GmbH is under license. Othear trademarks and trade names are those of their respective owners.