



Main

Range of product	Altivar
Product or component type	Encoder interface card
Range compatibility	Altivar Lift Altivar 61 Altivar 71Q Altivar 71 Altivar 61Q
Discrete output type	Differential
Communication port protocol	RS422
[Us] rated supply voltage	5 V DC (voltage limits: 5...5.5 V)
Number of pulses per revolution	10000 ATV71H.....383 5000 all ATV61 drives 5000 ATV71H...M3 5000 ATV71H...M3X 5000 ATV71H...N4

Complementary

Maximum supply current	0.2 A
Protection type	Short-circuit protection Overload protection
Maximum cable distance between devices	164.04 ft (50 m)
Maximum operating frequency	300 kHz
Input signal	A B Compliment of A Compliment of B
Input impedance	440 Ohm
Electrical connection	Terminal, connection capacity: 0.2 mm ² (AWG 24) <25 m cable length, encoder, 100 mA at 4.5 V Terminal, connection capacity: 0.5 mm ² (AWG 20) <25 m cable length, encoder, 200 mA at 4.5 V Terminal, connection capacity: 0.5 mm ² (AWG 20) <50 m cable length, encoder, 100 mA at 4.5 V Terminal, connection capacity: 0.75 mm ² (AWG 18) <50 m cable length, encoder, 200 mA at 4.5 V
Net Weight	0.44 lb(US) (0.2 kg)

Ordering and shipping details

Category	22135 - ATV61-71 ACCESSORIES
Discount Schedule	CP4C
GTIN	00785901807179
Nbr. of units in pkg.	1
Package weight(Lbs)	0.36 lb(US) (0.16 kg)
Returnability	Yes
Country of origin	ID

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.95 in (7.5 cm)
Package 1 width	6.69 in (17 cm)
Package 1 Length	9.06 in (23 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	7
Package 2 Weight	3.37 lb(US) (1.528 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------