

## Micrometer

small measuring faces

Mitutoyo

### Application:

For measuring narrow external recesses and grooves.

### Execution:

- Semi-gloss chrome-plated scale drum and sleeve
- Carbide-tipped measuring faces
- Friction coupling for consistent, repeatable measuring force

### Advantage:

- Accesses hard-to-reach measuring points

### Delivery:

Includes box, setting standard



<b>Art. no.</b>	<b>32016 525</b>
<b>Brand</b>	MITUTOYO
<b>Manufacturer Part Number</b>	111-115
<b>Min./max. length measuring range</b>	0-25 mm
<b>Vernier scale</b>	0.01 mm
<b>Measuring surface diameter</b>	3 mm
<b>Measuring surface depth</b>	10 mm
<b>Measuring spindle increments</b>	0.5 mm
<b>Bracket depth</b>	38 mm
<b>Spindle clamping</b>	Yes
<b>Error limit</b>	3 µm
<b>Display</b>	Nonius
<b>Min./max. measurement force</b>	5-10 N
<b>DIN</b>	863
<b>Calibration Group</b>	D
<b>Gross Weight</b>	0.295 kg
<b>Product Group</b>	3MA

### EAN

4946368008813